

PHILIPS

Saeco

Super-automatic
espresso machine

Royal

Royal

One Touch

Cappuccino

HD8930/04



So simple, so delicious

With large capacities and insulated milk container

The new Saeco Royal HD8930/01 is the rejuvenation of a trusted classic. What remains unchanged is the extremely solid performance and the generous tanks for beans, water and coffee grounds.

Easy to use

- Cup warmer
- Ergonomic in day-by-day operations
- Insulated milk container
- One touch beverage selection

Ease of cleaning and maintaining

- Always a clean machine thanks to auto-clean and descaling
- Dishwasher safe Cappuccinatore
- Easy cleaning stainless steel milk container

Coffee specialty customization

- Adjustable coffee length and intensity

High performance all day long

- Large capacity containers
- Milk specialties without the wait thanks to a double boiler

Highlights

Adjustable coffee length and



Choose your favorite coffee blend and adjust coffee length and intensity (temperature, pre-brewing, strength). Length: you can adjust the amount of brewed coffee according to your taste and/or the size of your cups. Temperature: the machine allows you to adjust via setting menu the temperature of your coffee. Pre-brewing: you can adjust via setting menu the time of pre-wetting of the coffee powder into the infusion chamber, in order to extract all the taste. Strength: the machine is set-up for adjusting the strength with the amount of coffee to be ground, using the specific lever on the side.

Auto cleaning and descaling



Saeco designed this espresso machine to automatically clean its coffee circuit with water upon starting up or switching off of the machine, this delivers a great, fresh taste with each cup of coffee. Regular descaling prolongs your espresso machine's life. This machine will not only prompt when descaling is needed, the automated descaling process will start on your machine and guides you with clear on-screen messages when you have to intervene. Descaling has never been so easy!

Cup warmer



This feature allows you to not only store your espresso cups and glasses right on the espresso machine, it also pre-heats them letting the aroma unfold even better and guaranteeing a long-lasting crema

Dishwasher safe Cappuccinatore



Keep the Saeco espresso machine at its best, by cleaning the automatic Cappuccinatore simply washing it with lukewarm water or directly into the dishwasher machine.

Professional double boiler



With 2 separate heating systems to cater for both the optimal coffee or milk frothing temperatures, this Saeco fully automatic espresso machine guarantees professional performance and speed everytime. You are able to prepare as many latte macchiatos and

cappuccinos as you wish, one after the other and each just as good as the previous without waiting.

Easy cleaning milk container




Easy cleaning stainless steel milk container

Ergonomic day-by-day



Saeco is a synonym for convenience: refilling beans or water, emptying the coffee-dump box or the drip tray, all compartments of the full automatic coffee machine are directly accessible.

Insulated milk container



Insulated milk container

Specifications

Technical specifications

Boiler material: Stainless steel (Inox)

Number of water boilers: 2 boilers (instant steam)

Water pressure in pump: 15 bar (perfect espresso)

Supported coffee types: Ground coffee, Whole coffee beans

Country of origin: Made in Italy, Designed in Italy

Removable brewing group

Power: 1400 W

Voltage: 220 V

Frequency: 50 Hz

Cord length: 80 cm

Sustainability

Automatic Stand-by Option

Perfect Espresso

Espresso technology: Aroma-system: pre-brewing, Cup warmer

Service

2-year worldwide guarantee

Easy to use

Cleaning and maintenance: Automatic milk circuit rinse, Descaling cycle

Usage: Adjustable coffee dispenser, Instant steam (2 boilers), Removable brewing group

Weight and dimensions

Product weight: 15 kg

Product dimensions (L x D x H): 336 x 380 x 450 mm

Coffee bean capacity: 350 gr

Waste container capacity: 20 servings

Milk carafe capacity: 0,5 l

Water tank capacity: 2.2 l

Features

Simultaneous brewing

Hot water wand

Design

Colour: Glossy Silver

Materials and finishing: Plastic Front/Top + Metal sides/rear

