

PHILIPS

Saeco

Super-automatic
espresso machine

Royal

Automatic Milk Frother

Silver

HD8930/13



Solid performance, cup after cup

With large capacity containers

The new Saeco Royal is the rejuvenation of a trusted classic. What remains unchanged is the extremely solid performance and the generous tanks for beans, water and coffee grounds.

Authentic Italian coffee perfection

- Delicious milk froth thanks to the automatic milk frother
- Milk specialties without the wait thanks to a double boiler

Set the beverages to suit your taste

- Save your favorite coffee settings
- Avoid heat loss and fit every cup with our adjustable spout

Ease of cleaning and maintaining

- Always a clean machine thanks to auto-clean and descaling
- Easy cleaning thanks to removable brewing group
- Easy cleaning thanks to dishwasher-safe parts

Highlights

Saves your coffee settings



You will always get a perfect cup of espresso brewed just for you, according to your personal preference, thanks to our innovative memo function to adjust the coffee length, strength and temperature. Enjoy a superb coffee drink in your favorite cup with just the press of a button.

Adjustable spout



The adjustable spout on our espresso machines will fit every cup and thus prevents the coffee splashing or cooling down while pouring in your cup. This way your espresso is always served at the right temperature while maintaining a clean machine.

Dishwasher-safe parts



For your convenience, you can put the Saeco's drip tray and milk frother or milk carafe in the dishwasher. This will save time and ensure a hygienic cleaning.

Removable brewing group



The brewing group, a Saeco invention, is the heart of our espresso machines, ensuring automation. The brewing group is, depending on the model, easily accessible from the front or side. It can be removed effortlessly for easily cleaning by rinsing under the tap ensuring maximum hygiene.

Auto cleaning and descaling



Saeco designed this espresso machine to automatically clean its coffee circuit with water upon starting up or switching off of the machine, this delivers a great, fresh taste with

each cup of coffee. Regular descaling prolongs your espresso machine's life. This machine will not only prompt when descaling is needed, the automated descaling process will start on your machine and guides you with clear on-screen messages when you have to intervene. Descaling has never been so easy!

Automatic milk frother



Preparing a tasty cappuccino is easy with this Saeco espresso machine thanks to the automatic milk frother, which baristas also call "cappuccinatore". The milk frother will draw milk directly from a milk carton or jug and froth it automatically, dispensing it directly into your cup. With just one touch you will instantly get a delicious and creamy froth.

Professional double boiler



With 2 separate heating systems to cater for both the optimal coffee or milk frothing temperatures, this Saeco fully automatic espresso machine guarantees professional performance and speed everytime. You are able to prepare as many latte macchiatos and cappuccinos as you wish, one after the other and each just as good as the previous without waiting.

Specifications

Technical specifications

Boiler material: Stainless steel (Inox)

Number of water boilers: 2 boilers (instant steam)

Water pressure in pump: 15 bar (perfect espresso)

Supported coffee types: Ground coffee, Whole coffee beans

Country of origin: Made in Italy, Designed in Italy

Removable brewing group

Power: 1400 W

Voltage: 240 V

Frequency: 60 Hz

Cord length: 80 cm

Sustainability

Automatic Stand-by Option

Perfect Espresso

Espresso technology: Aroma-system: pre-brewing, Cup warmer

Service

2-year worldwide guarantee

Easy to use

Cleaning and maintenance: Automatic milk circuit rinse, Descaling cycle

Usage: Adjustable coffee dispenser, Instant steam (2 boilers), Removable brewing group

Weight and dimensions

Product weight: 15 kg

Product dimensions (L x D x H): 336 x 380 x 450 mm

Coffee bean capacity: 350 gr

Waste container capacity: 20 servings

Milk carafe capacity: 0,5 l

Water tank capacity: 2.2 l

Features

Simultaneous brewing

Hot water wand

Design

Colour: Glossy Silver

Materials and finishing: Plastic Front/Top + Metal sides/rear

