

PHILIPS

Saeco

Super-automatic
espresso machine

Xelsis

Focus



HD8942/03



Love your own favorite coffee specialty Up to 9 fully customizable coffee specialties

With the Xelsis each and every family member can enjoy his or her favorite coffee specialty. Up to 9 coffee specialties can be fully personalized.

Multi beverage

- Up to 9 fully customizable coffee specialties
- Perfect milk froth thanks to the integrated milk carafe

Bean- to-cup customization

- Boost coffee crema and body
- Patented intelligent adjustable milk froth
- Full bean-to-cup customization

Easy to use

- Immediate beverage selection
- Ergonomic in day-by-day operations

Ease of cleaning and maintaining

- Always a clean machine thanks to auto-clean and descaling
- Frontal access to removable brewing group



asimpleswitch.com

Highlights

Crema and body boost



This Saeco features our patented crema and body boost. This dial, conveniently located at your machine's spout, allows you to smoothly adjust the counter pressure changing your espresso's body and crema. Try it yourself and find your favorite taste.

Adjustable milk froth



Only Saeco coffee machine offers an intelligent milk froth adjustment system. Simply select the level of froth you'd like via the beverage menu.

Auto cleaning and descaling



Saeco designed this espresso machine to automatically clean its coffee circuit with water upon starting up or switching off of the machine, this delivers a great, fresh taste with each cup of coffee. Regular descaling prolongs your espresso machine's life. This machine will not only prompt when descaling is needed, the automated descaling process will start on your

machine and guides you with clear on-screen messages when you have to intervene. Descaling has never been so easy!

Removable brewing group



The brewing group is at the heart of every fully automatic coffee machine and it should always be kept clean. A task that doesn't get any more convenient than with a Saeco: remove, rinse and re-insert – finished.

Full customization



Everything just the way you like it: With this coffee machine you can choose your favorite coffee blend and adjust coffee length, intensity, temperature, crema and body structure until they all meet your personal taste perfectly.

Ergonomic day-by-day



Saeco is a synonym for convenience: refilling beans or water, emptying the coffee-dump box or the drip tray, all compartments of the full automatic coffee machine are directly accessible.

Immediate beverage selection



Whether you want a cappuccino or an espresso, with the immediate beverage selection you can enjoy your personally customized beverage specialty at the touch of a button

9 personalized beverages

With Saeco Xelsis you have a wide choice of beverages from espresso to latte macchiato. You can personalize each coffee specialty, adjusting both coffee and milk settings, as you like.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Technical specifications

Number of water boilers: 2 boilers (instant steam)

Supported coffee types: Ground coffee, Whole coffee beans

Service

2-year worldwide guarantee

Perfect Espresso

Espresso technology: Saeco adapting system, Aroma-system: pre-brewing, SBS: creme adaptor

Multi-Beverage

Milk Variations: Frothing degree adaptor, Integrated auto milk function, Milk quantity selector, Removable milk carafe

Easy to use

Cleaning and maintenance: Automatic coffee circuit rinse, Automatic milk circuit rinse, Descaling cycle

Usage: Adjustable coffee dispenser, Bypass for grinded coffee, Cup holding surface, Frontal access to all function, Instant steam (2 boilers), Removable brewing group, Removable watertank

Energy saving

Energy saving: Selectable Eco-mode

Technical data

Boiler: Stainless steel

Frequency: 50 Hz

Power: 1500 W

Voltage: 240 V

Pump Pressure: 15 bar

Weight and dimensions

Product dimensions (L x D x H): 280x370x420 mm

Maximum cup height: 150 mm

Weight: 13,9 kg

Coffee bean capacity: 350 gr

Waste container capacity: 14 servings

Milk carafe capacity: 0.5 L

Water tank capacity: 1.6 L

