

PHILIPS

Saeco

Super-automatic
espresso machine

Syntia

Xelsis

Focus



HD8942/12



Love your own favourite coffee speciality

Up to 9 fully customisable coffee specialities

With the Xelsis, each and every family member can enjoy his or her favourite coffee speciality. Up to 9 coffee specialities can be fully personalised.

Multi-beverage

- Up to 9 fully customisable coffee specialities
- Perfect milk froth thanks to the integrated milk carafe

Bean- to-cup customisation

- Boost coffee crema and body
- Patented intelligent adjustable milk froth
- Full bean-to-cup customisation

Easy to use

- Immediate beverage selection
- Ergonomic in day to day operation

Easy to clean and maintain

- Always a clean machine thanks to auto-clean and descaling
- Frontal access to removable brewing group

Highlights

Crema and body boost



This Saeco features our patented crema and body boost. This dial, conveniently located at your machine's spout, allows you to smoothly adjust the counter pressure, changing your espresso's body and crema. Try it yourself and find your favourite taste.

Adjustable milk froth



Only the Saeco coffee machine offers an intelligent milk froth adjustment system. Simply select the level of froth you'd like via the beverage menu.

Immediate beverage selection



Whether you want a cappuccino or an espresso, with the immediate beverage selection you can enjoy your personally customised beverage speciality at the touch of a button

Auto-cleaning and descaling



Saeco designed this espresso machine to automatically clean its coffee circuit with water when starting up or switching off to deliver a great, fresh taste with each cup of coffee. Regular descaling prolongs your espresso machine's life. This machine will not only prompt when descaling is needed, the automated descaling process will start and guide you with clear on-screen messages when you have to intervene. Descaling has never been so easy!

Removable brewing group



The brewing group is at the heart of every fully automatic coffee machine and it should always be kept clean. A task that doesn't get any more convenient than with a Saeco: remove, rinse and re-insert — finished.

Full customisation



Everything just the way you like it: With this coffee machine you can choose your favourite coffee blend and adjust coffee length,

intensity, temperature, crema and body structure until they all meet your personal taste perfectly.

Ergonomic day to day



Saeco is a synonym for convenience: refilling beans or water, emptying the coffee-dump box or the drip tray, all compartments of the full automatic coffee machine are directly accessible.

9 personalised beverages

With Saeco Xelsis you have a wide choice of beverages from espresso to latte macchiato. You can personalise each coffee speciality, adjusting both coffee and milk settings to how you want them.

Integrated milk carafe



Enjoy your milk specialities with the automated milk carafe with auto-clean. Simply pour milk into the carafe, plug it into the machine and select your preferred coffee drink. Whether it is a latte macchiato, cappuccino or caffelatte, your drink will be served within seconds. The carafe of your Saeco espresso machine conveniently comes with auto-clean, which means two automatic steam-rinsing cycles will clean your carafe's tubes after every use for a fresh milk taste every time.

Specifications

Technical specifications

Boiler material: Stainless steel (Inox)

Number of water boilers: 2 boilers (instant steam)

Water pressure in pump: 15 bar (perfect espresso)

Supported coffee types: Ground coffee, Whole coffee beans

Country of origin: Made in Italy, Designed in Italy

Removable brewing group

Power: 1500 W

Voltage: 230 V

Frequency: 50 Hz

Cord length: 80 cm

Sustainability

Automatic Standby Option

Perfect Espresso

Espresso technology: Saeco adapting system, Aroma-system: pre-brewing, SBS: creme adaptor, Cup warmer

Service

2-year worldwide guarantee

Multi-Beverage

Milk Variations: Frothing degree adaptor, Integrated auto milk function, Milk quantity selector, Removable milk carafe

Easy to use

Cleaning and maintenance: Automatic coffee circuit rinse, Automatic milk circuit rinse, Descaling cycle

Usage: Adjustable coffee dispenser, Bypass for grinded coffee, Cup-holding surface, Frontal

access to all functions, Instant steam (2 boilers), Removable brewing group, Removable water tank

Weight and dimensions

Maximum cup height: 150 mm

Product weight: 13.9 kg

Product dimensions (L x D x H): 280 x 370 x 420 mm

Coffee bean capacity: 350 gr

Waste container capacity: 14 servings

Milk carafe capacity: 0.5 l

Water tank capacity: 1.6 l

