

PHILIPS

Saeco

Super-automatic
espresso machine

Xelsis

Class

White



HD8943/22



Love your own favourite coffee speciality

Multi beverage, Multi user

With the Xelsis each and every family member can enjoy his or her favourite coffee speciality. Thanks to the unique multi-user function up to 6 personal user profiles can be created and for each profile up to 9 beverages can be personalised.

Multi-user and Multi-beverage

- 6 unique user profiles for 9 beverages
- Perfect milk froth thanks to the integrated milk carafe

Bean- to-cup customisation

- Boost coffee crema and body
- Patented intelligent adjustable milk froth
- Full bean-to-cup customisation

Easy to use

- Dynamic multi-media user interface
- Ergonomic in day to day operation

Easy to clean and maintain

- Always a clean machine thanks to auto-clean and descaling
- Frontal access to removable brewing group

Highlights

Crema and body boost



This Saeco features our patented crema and body boost. This dial, conveniently located at your machine's spout, allows you to smoothly adjust the counter pressure, changing your espresso's body and crema. Try it yourself and find your favourite taste.

6 users x 9 beverages



With this coffee machine up to 9 coffee specialities can be personalised by 6 different users – every family member gets his or her own favourite customised speciality with just one touch

Adjustable milk froth




Only the Saeco coffee machine offers an intelligent milk froth adjustment system. Simply select the level of froth you'd like via the beverage menu.

Auto-cleaning and descaling



Saeco designed this espresso machine to automatically clean its coffee circuit with water when starting up or switching off to deliver a great, fresh taste with each cup of coffee. Regular descaling prolongs your espresso machine's life. This machine will not only prompt when descaling is needed, the automated descaling process will start and guide you with clear on-screen messages when you have to intervene. Descaling has never been so easy!

Multi-media user interface



The wide colour TFT screen allows colourful and dynamic pictures to always know exactly what the coffee machine is doing or what it needs

Removable brewing group



The brewing group is at the heart of every fully automatic coffee machine and it should always be kept clean. A task that doesn't get any more convenient than with a Saeco: remove, rinse and re-insert — finished.

Full customisation



Everything just the way you like it: With this coffee machine you can choose your favourite coffee blend and adjust coffee length, intensity, temperature, crema and body structure until they all meet your personal taste perfectly.

Ergonomic day to day



Saeco is a synonym for convenience: refilling beans or water, emptying the coffee-dump box or the drip tray, all compartments of the full automatic coffee machine are directly accessible.

Integrated milk carafe



Enjoy your milk specialities with the automated milk carafe with auto-clean. Simply pour milk into the carafe, plug it into the machine and select your preferred coffee drink. Whether it is a latte macchiato, cappuccino or caffelatte, your drink will be served within seconds. The carafe of your Saeco espresso machine conveniently comes with auto-clean, which means two automatic steam-rinsing cycles will clean your carafe's tubes after every use for a fresh milk taste every time.

Specifications

Perfect Espresso

Espresso technology: Saeco adapting system, Aroma-system: pre-brewing, SBS: creme adaptor, Cup warmer

Multi-Beverage

Milk Variations: Frothing degree adaptor, Integrated auto milk function, Milk Island compatible, Milk quantity selector, Removable milk carafe

Easy to use

Cleaning and maintenance: Automatic coffee circuit rinse, Automatic milk circuit rinse, Descaling cycle

Usage: Adjustable coffee dispenser, Bypass for

grinded coffee, Cup-holding surface, Frontal access to all functions, Instant steam (2 boilers), Removable brewing group, Removable water tank

Energy saving

Energy saving: Selectable Eco-mode

Technical data

Boiler: Stainless steel

Frequency: 50 Hz

Power: 1500 W

Voltage: 230 V

Pump Pressure: 15 Bar

Weight and dimensions

Maximum cup height: 150 mm

Product dimensions (L x D x H): 280 x 370 x 420 mm

Weight: 15.8 kg

Coffee bean capacity: 350 gr

Dump box capacity: 14 servings

Milk carafe capacity: 0.5 l

Water tank capacity: 1.6 l

