

# PHILIPS

## Saeco

Super-automatic  
espresso machine

Xelsis

Integrated milk jug & frother

Stainless steel



HD8944/01



## Multi-beverage, multi-user with full automated dual cleaning milk carafe

With the Saeco Xelsis coffee machine every family member can enjoy his or her favorite coffee. Thanks to the unique multi-user function up to 6 personal user profiles can be created and for each profile up to 9 beverages can be personalized

### Authentic Italian coffee perfection

- Perfect milk froth thanks to the integrated milk carafe
- Milk specialties without the wait thanks to a double boiler
- Coffee without burnt taste thanks to 100% ceramic grinders

### Set the beverages to suit your taste

- Personalize your coffee in 6 user profiles
- Play with the coffee's richness with our adjustable grinders
- Boost coffee crema and body

### Ease of cleaning and maintaining

- Always a clean machine thanks to auto-clean and descaling
- Hygienic milk frothing thanks to automated dual cleaning
- Easy cleaning thanks to removable brewing group
- Cutting-edge design with stainless steel finish

# Highlights

## Stainless steel



The cutting-edge design of your Saeco espresso machine is rounded off by the stainless steel finish. The stainless steel provides a high quality look and will be a highlight on your kitchen counter tops. It also gives greater resistance for a long-lasting performance.

## 100% ceramic grinders



This espresso machine is equipped 100% ceramic grinders. Saeco uses ceramic grinders because of their consistent grind without overheating the coffee bean for an impeccable espresso. Ceramic also ensures long-lasting performance and a totally silent operation.

## 8 step adjustable grinders



Different coffee blends require different levels of granularity for the full flavor to unfold. The grind granularity of this espresso machine can be adjusted in 8 settings, from the finest grind, for a full bodied espresso, to the coarsest, for a lighter coffee.

## 6 user profiles



This Saeco espresso machine comes with 6 customizable profiles that memorize your personal preference for different coffee drinks. This makes it very easy to get a perfect tailor-made cup of coffee although you are not the only one using the machine.

## Removable brewing group



The brewing group, a Saeco invention, is the heart of our espresso machines, ensuring automation. The brewing group is, depending on the model, easily accessible from the front or side. It can be removed effortlessly for easily cleaning by rinsing under the tap ensuring maximum hygiene.

## Automatic dual cleaning carafe



This Saeco espresso machine comes with a fully automated dual clean function for its milk carafe. The dual cleaning uses two independent steam cycles to swiftly rinse your

milk carafe after each coffee drink you prepare, for a fresh milk drink everytime. Hygienic milk frothing was never this easy.

## Auto cleaning and descaling



Saeco designed this espresso machine to automatically clean its coffee circuit with water upon starting up or switching off of the machine, this delivers a great, fresh taste with each cup of coffee. Regular descaling prolongs your espresso machine's life. This machine will not only prompt when descaling is needed, the automated descaling process will start on your machine and guides you with clear on-screen messages when you have to intervene. Descaling has never been so easy!

## Professional double boiler



With 2 separate heating systems to cater for both the optimal coffee or milk frothing temperatures, this Saeco fully automatic espresso machine guarantees professional performance and speed everytime. You are able to prepare as many latte macchiatos and cappuccinos as you wish, one after the other and each just as good as the previous without waiting.

# Specifications

## Perfect Espresso

**Espresso technology:** Saeco adapting system, Aroma-system: pre-brewing, SBS: creme adaptor, Cup warmer

## Multi-Beverage

**Milk Variations:** Frothing degree adaptor, Integrated auto milk function, Milk quantity selector, Removable milk carafe

## Easy to use

**Cleaning and maintenance:** Automatic coffee circuit rinse, Automatic milk circuit rinse, Descaling cycle

**Usage:** Adjustable coffee dispenser, Bypass for

grinded coffee, Cup holding surface, Frontal access to all function, Instant steam (2 boilers), Removable brewing group, Removable watertank

## Energy saving

**Energy saving:** Selectable Eco-mode

## Technical data

**Boiler:** Stainless steel

**Frequency:** 50 Hz

**Power:** 1500 W

**Voltage:** 230 V

**Pump Pressure:** 15 bar

## Weight and dimensions

**Maximum cup height:** 150 mm

**Product dimensions (L x D x H):** 280x370x420 mm

**Weight:** 16,1 kg

**Coffee bean capacity:** 350 gr

**Dump box capacity:** 14 servings

**Milk carafe capacity:** 0.5 l

**Water tank capacity:** 1.6 l

