

PHILIPS

Saeco

Automatic espresso machine

Xelsis

Stainless Steel



HD8944/01



Love your own favorite coffee specialty Multi beverage, Multi user

With the Xelsis each and every family member can enjoy his or her favorite coffee specialty. Thanks to the unique multi-user function up to 6 personal user profiles can be created and for each profile up to 9 beverages can be personalized.

Multi-user and Multi-beverage

- 6 unique user profiles for 9 beverages
- Integrated automatic milk function with Autoclean

Bean- to-cup customization

- SBS: patented adjustable espresso crema and body structure
- Patented intelligent adjustable milk froth
- Full bean-to-cup customization

Easy to use

- Dynamic multi-media user interface
- Ergonomic in day-by-day operations

Easy to clean and maintain

- Automatic cleaning and de-scaling
- Frontal access to removable brewing group

Highlights

SBS (Saeco Brewing System)



Philips Saeco exclusively allows you to adjust your espresso's intensity, altering the crema and body structure as it is dispensed. Simply by turning the knob you can prepare the crema exactly according to your taste. A little knob that makes a big difference.

Autocleaning and de-scaling



Easy to use includes easy maintenance: Thanks to the automatic cleaning and de-scaling cycles, you are guaranteed perfect enjoyment every day and maximum longevity for your machine.

Full customization




Everything just the way you like it: Choose your favorite coffee blend and adjust coffee length, intensity, temperature, crema and body structure until they all meet your personal taste perfectly.

6 users x 9 beverages



Up to 9 coffee specialties can be personalized by 6 different users – every family member gets his or her own favorite customized specialty with just one touch

Multi-media user interface



The wide color TFT screen allows colorful and dynamic pictures to always know exactly what the machine is doing or what it needs

Ergonomic day-by-day



Philips-Saeco is a synonym for convenience: refilling beans or water, emptying the coffee-dump box or the drip tray, all compartments are directly accessible.

Adjustable milk froth



Only Philips Saeco offers an intelligent milk froth adjustment system. Simply select the level of froth you'd like via the beverage menu.

Removable brewing group



The brewing group is at the heart of every fully automatic coffee machine and it should always be kept clean. A task that doesn't get any more convenient than with a Saeco: remove, rinse and re-insert – finished.

Integrated milk function



Integrated automatic milk function with Autoclean

Specifications

Perfect Espresso

Espresso technology: Saeco adapting system, Aroma-system: pre-brewing, SBS: creme adaptor, Cup warmer

Multi-Beverage

Milk Variations: Frothing degree adaptor, Integrated auto milk function, Milk quantity selector, Removable milk carafe

Easy to use

Cleaning and maintenance: Automatic coffee circuit rinse, Automatic milk circuit rinse, Descaling cycle

Usage: Adjustable coffee dispenser, Bypass for

grinded coffee, Cup holding surface, Frontal access to all function, Instant steam (2 boilers), Removable brewing group, Removable watertank

Energy saving

Energy saving: Selectable Eco-mode

Technical data

Boiler: Stainless steel

Frequency: 50 Hz

Power: 1500 W

Voltage: 230 V

Pump Pressure: 15 bar

Weight and dimensions

Product dimensions (L x D x H): 280x370x420 mm

Weight: 16,1 kg

Coffee bean capacity: 350 gr

Dump box capacity: 14 servings

Milk carafe capacity: 0.5 l

Water tank capacity: 1.6 l

