

PHILIPS

Saeco

Super-automatic
espresso machine

Xelsis

Stainless Steel

Integrated Milk Carafe

Stainless steel



HD8944/09



Multi-beverage, multi-user with fully automated dual cleaning milk carafe

With the Xelsis espresso machine, each family member can enjoy his or her favourite coffee. Thanks to the unique multi-user function, up to 6 personal user profiles can be created, and for each profile up to 9 beverages can be personalised.

Authentic Italian coffee perfection

- Perfect milk froth thanks to the integrated milk carafe
- Milk specialities without the wait thanks to a double boiler
- Coffee without burnt taste thanks to 100% ceramic grinders

Set the beverages to suit your taste

- Personalise your coffee in 6 user profiles
- Play with the coffee's richness with our adjustable grinders
- Boost coffee crema and body

Easy to clean and maintain

- Always a clean machine thanks to auto-clean and descaling
- Hygienic milk frothing thanks to automated dual cleaning
- Easy cleaning thanks to removable brewing group
- Cutting-edge design with stainless steel finish

Highlights

Stainless steel



The cutting-edge design of your Saeco espresso machine is rounded off by the stainless steel finish. The stainless steel provides a high-quality look and will be a highlight on your kitchen counter tops. It also gives greater resistance for a long-lasting performance.

100% ceramic grinders




This espresso machine is equipped with 100% ceramic grinders. Saeco uses ceramic grinders because of their consistent grind without overheating the coffee bean, for an impeccable espresso. Ceramic also ensures long-lasting performance and totally silent operation.

8-step adjustable grinders



Different coffee blends require different levels of granularity for the full flavour to unfold. The grind granularity of this espresso machine can be adjusted in 8 settings, from the finest grind, for a full-bodied espresso, to the coarsest, for a lighter café crème.

6 user profiles



This Saeco espresso machine comes with 6 customisable profiles that memorise your personal preference for different coffee drinks. This makes it very easy to get a perfect tailor-made cup of coffee, even if you are not the only one using the machine.

Removable brewing group



The brewing group, a Saeco invention, is the heart of our espresso machines, ensuring automation. The brewing group is, depending on the model, easily accessible from the front or side. It can be removed effortlessly for easy cleaning by rinsing under the tap, ensuring maximum hygiene.

Automatic dual-cleaning carafe



This Saeco espresso machine comes with a fully automated dual-clean function for its milk carafe. The dual cleaning uses two independent steam cycles to swiftly rinse your

milk carafe after each coffee drink you prepare, for a fresh milk drink every time. Hygienic milk frothing has never been this easy.

Auto-cleaning and descaling



Saeco designed this espresso machine to automatically clean its coffee circuit with water when starting up or switching off to deliver a great, fresh taste with each cup of coffee. Regular descaling prolongs your espresso machine's life. This machine will not only prompt when descaling is needed, the automated descaling process will start and guide you with clear on-screen messages when you have to intervene. Descaling has never been so easy!

Professional double boiler



With 2 separate heating systems to cater for both the optimal coffee temperature and the milk frothing temperature, this Saeco fully automatic espresso machine guarantees professional performance and speed every time. You are able to prepare as many latte macchiatos and cappuccinos as you wish, one after the other and each just as good as the previous one, without waiting.

Specifications

Perfect Espresso

Espresso technology: Saeco adapting system, Aroma-system: pre-brewing, SBS: creme adaptor, Cup warmer

Multi-Beverage

Milk Variations: Frothing degree adaptor, Integrated auto milk function, Milk quantity selector, Removable milk carafe

Easy to use

Cleaning and maintenance: Automatic coffee circuit rinse, Automatic milk circuit rinse, Descaling cycle

Usage: Adjustable coffee dispenser, Bypass for

grinded coffee, Cup-holding surface, Frontal access to all functions, Instant steam (2 boilers), Removable brewing group, Removable water tank

Energy saving

Energy saving: Selectable Eco-mode

Technical data

Boiler: Stainless steel

Frequency: 50 Hz

Power: 1500 W

Voltage: 230 V

Pump Pressure: 15 Bar

Weight and dimensions

Maximum cup height: 150 mm

Product dimensions (L x D x H): 280 x 370 x 420 mm

Weight: 16.1 kg

Coffee bean capacity: 350 gr

Dump box capacity: 14 servings

Milk carafe capacity: 0.5 l

Water tank capacity: 1.6 l

