

# PHILIPS

## Saeco

Super-automatic  
espresso machine

Xelsis

Xelsis

Integrated milk jug & frother

Stainless Steel



HD8944/13



## Love your own favorite coffee specialty Multi beverage, Multi user

With the Xelsis each and every family member can enjoy his or her favorite coffee specialty. Thanks to the unique multi-user function up to 6 personal user profiles can be created and for each profile up to 9 beverages can be personalized.

### Multi-user and Multi-beverage

- 6 unique user profiles for 9 beverages
- Perfect milk froth thanks to the integrated milk carafe

### Bean- to-cup customization

- Boost coffee crema and body
- Patented intelligent adjustable milk froth
- Full bean-to-cup customization

### Easy to use

- Dynamic multi-media user interface
- Ergonomic in day-by-day operations

### Ease of cleaning and maintaining

- Always a clean machine thanks to auto-clean and descaling
- Frontal access to removable brewing group

# Highlights

## Crema and body boost



This Saeco features our patented crema and body boost. This dial, conveniently located at your machine's spout, allows you to smoothly adjust the counter pressure changing your espresso's body and crema. Try it yourself and find your favorite taste.

## 6 users x 9 beverages



With this coffee machine up to 9 coffee specialties can be personalized by 6 different users – every family member gets his or her own favorite customized specialty with just one touch.

## Adjustable milk froth




Only Saeco coffee machine offers an intelligent milk froth adjustment system. Simply select the level of froth you'd like via the beverage menu.

## Auto cleaning and descaling



Saeco designed this espresso machine to automatically clean its coffee circuit with water upon starting up or switching off of the machine, this delivers a great, fresh taste with each cup of coffee. Regular descaling prolongs your espresso machine's life. This machine will not only prompt when descaling is needed, the automated descaling process will start on your machine and guides you with clear on-screen messages when you have to intervene. Descaling has never been so easy!

## Multi-media user interface



The wide color TFT screen allows colorful and dynamic pictures to always know exactly what the coffee machine is doing or what it needs.

## Removable brewing group



The brewing group is at the heart of every fully automatic coffee machine and it should always be kept clean. A task that doesn't get any more convenient than with a Saeco: remove, rinse and re-insert – finished.

## Full customization



Everything just the way you like it: With this coffee machine you can choose your favorite coffee blend and adjust coffee length, intensity, temperature, crema and body structure until they all meet your personal taste perfectly.

## Ergonomic day-by-day



Saeco is a synonym for convenience: refilling beans or water, emptying the coffee-dump box or the drip tray, all compartments of the full automatic coffee machine are directly accessible.

## Integrated milk carafe



Enjoy your milk specialties with the automated milk carafe with auto-clean. Simply pour milk into the carafe, plug it into the machine and select your preferred coffee drink. Whether it is a latte macchiato, cappuccino or caffelatte, your drink will be served within seconds. The carafe of your Saeco espresso machine conveniently comes with auto-clean, which means two automatic steam-rinsing cycles will clean your carafe's tubes after every use for a fresh milk taste everytime.

# Specifications

## Technical specifications

**Boiler material:** Stainless steel (Inox)

**Pump pressure:** 15

**Number of water boilers:** 2 boilers (instant steam)

**Water pressure in pump:** 15 bar (perfect espresso)

**Supported coffee types:** Ground coffee, Whole coffee beans

**Country of origin:** Made in Italy, Designed in Italy

**Power:** 1500 W

**Voltage:** 240 V

**Frequency:** 50 Hz

## Sustainability

Automatic Stand-by Option

## Perfect Espresso

**Espresso technology:** Saeco adapting system, Aroma-system: pre-brewing, SBS: creme adaptor, Cup warmer

## Service

2-year worldwide guarantee

## Multi-Beverage

**Milk Variations:** Frothing degree adaptor, Integrated auto milk function, Milk quantity selector, Removable milk carafe

## Easy to use

**Cleaning and maintenance:** Automatic coffee circuit rinse, Automatic milk circuit rinse, Descaling cycle

**Usage:** Adjustable coffee dispenser, Bypass for

grinded coffee, Cup holding surface, Frontal access to all function, Instant steam (2 boilers), Removable brewing group, Removable watertank

## Weight and dimensions

**Maximum cup height:** 150 mm

**Product weight:** 16.1 kg

**Product dimensions (L x D x H):** 280 x 370 x 420 mm

**Coffee bean capacity:** 350 gr

**Waste container capacity:** 14 servings

**Milk carafe capacity:** 0.5 L

**Water tank capacity:** 1.6 L

