

PHILIPS

Saeco

Super-automatic
espresso machine

Xelsis

Integrated milk jug & frother

Mirror Stainless Steel



HD8946/03



Multi-beverage, multi-user with full automated dual cleaning milk carafe

With the Xelsis each and every family member can enjoy his or her favorite coffee specialty. Thanks to the unique multi-user function up to 6 personal user profiles can be created and for each profile up to 9 beverages can be personalized.

Authentic Italian coffee perfection

- Perfect milk froth thanks to the integrated milk carafe
- Milk specialties without the wait thanks to a double boiler
- Coffee without burnt taste thanks to 100% ceramic grinders

Set the beverages to suit your taste

- Personalize your coffee in 6 user profiles
- Play with the coffee's richness with our adjustable grinders
- Boost coffee crema and body

Ease of cleaning and maintaining

- Always a clean machine thanks to auto-clean and descaling
- Hygienic milk frothing thanks to automated dual cleaning



asimpleswitch.com

Highlights

100% ceramic grinders



This espresso machine is equipped 100% ceramic grinders. Saeco uses ceramic grinders because of their consistent grind without overheating the coffee bean for an impeccable espresso. Ceramic also ensures long-lasting performance and a totally silent operation.

8 step adjustable grinders



Different coffee blends require different levels of granularity for the full flavor to unfold. The grind granularity of this espresso machine can be adjusted in 8 settings, from the finest grind, for a full bodied espresso, to the coarsest, for a lighter coffee.

6 user profiles



This Saeco espresso machine comes with 6 customizable profiles that memorize your personal preference for different coffee drinks. This makes it very easy to get a perfect tailor-made cup of coffee although you are not the only one using the machine.

Automatic dual cleaning carafe



This Saeco espresso machine comes with a fully automated dual clean function for its milk carafe. The dual cleaning uses two independent steam cycles to swiftly rinse your milk carafe after each coffee drink you prepare, for a fresh milk drink everytime. Hygienic milk frothing was never this easy.

Auto cleaning and descaling



Saeco designed this espresso machine to automatically clean its coffee circuit with water upon starting up or switching off of the machine, this delivers a great, fresh taste with each cup of coffee. Regular descaling prolongs your espresso machine's life. This machine will not only prompt when descaling is needed, the automated descaling process will start on your machine and guides you with clear on-screen messages when you have to intervene. Descaling has never been so easy!

Professional double boiler



With 2 separate heating systems to cater for both the optimal coffee or milk frothing temperatures, this Saeco fully automatic

espresso machine guarantees professional performance and speed everytime. You are able to prepare as many latte macchiatos and cappuccinos as you wish, one after the other and each just as good as the previous without waiting.

Integrated milk carafe



Enjoy your milk specialties with the automated milk carafe with auto-clean. Simply pour milk into the carafe, plug it into the machine and select your preferred coffee drink. Whether it is a latte macchiato, cappuccino or caffelatte, your drink will be served within seconds. The carafe of your Saeco espresso machine conveniently comes with auto-clean, which means two automatic steam-rinsing cycles will clean your carafe's tubes after every use for a fresh milk taste everytime.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Technical specifications

Boiler material: Stainless steel (Inox)

Number of water boilers: 2 boilers (instant steam)

Water pressure in pump: 15 bar (perfect espresso)

Supported coffee types: Ground coffee, Whole coffee beans

Country of origin: Made in Italy, Designed in Italy

Removable brewing group

Power: 1500 W

Voltage: 240 V

Frequency: 50 Hz

Cord length: 80 cm

Sustainability

Automatic Stand-by Option

Perfect Espresso

Espresso technology: Saeco adapting system, Aroma-system: pre-brewing, SBS: creme adaptor, Cup warmer

Service

2-year worldwide guarantee

Multi-Beverage

Milk Variations: Frothing degree adaptor, Integrated auto milk function, Milk quantity selector, Removable milk carafe

Easy to use

Cleaning and maintenance: Automatic coffee circuit rinse, Automatic milk circuit rinse, Descaling cycle

Usage: Adjustable coffee dispenser, Bypass for grinded coffee, Cup holding surface, Frontal

access to all function, Instant steam (2 boilers), Removable brewing group, Removable watertank

Weight and dimensions

Maximum cup height: 150 mm

Product weight: 16.1 kg

Product dimensions (L x D x H): 280 x 370 x 420 mm

Coffee bean capacity: 350 gr

Waste container capacity: 14 servings

Milk carafe capacity: 0.5 L

Water tank capacity: 1.6 L

