



**Saeco Xelsis Evo  
Super-automatic  
espresso machine**

- Brews 8 coffee varieties
- Integrated milk jug & frother
- Stainless steel
- 8 step adjustable grinder



**HD8954/47**

## Multi-beverage, multi user

With full automated dual cleaning milk carafe

With Xelsis Evo espresso machine every family member can enjoy his or her favorite coffee. Thanks to the unique multi-user function up to 6 personal user profiles can be created and for each profile up to 9 beverages can be personalized.

**Advanced technology designed for coffee perfection**

- 20,000 cups of finest coffee with durable ceramic grinders

**High comfort is part of the experience**

- The fully removable brewing group can be cleaned in no time
- Proven hygiene with the patented steam cleaning carafe

**A variety of coffees customized to your taste**

- Fine-tune the coffee's richness with 8 grinder settings
- Save your favorite coffee with 6 user profiles

**Set the beverages to suit your taste**

- Boost coffee crema and body

**Authentic Italian coffee perfection**

- Perfect froth thanks to the dual chamber milk carafe
- Saeco adapting system: automated grinding adaptation
- Milk specialties without the wait thanks to a double boiler

 **Saeco**

**PHILIPS**

Saeco, a Philips brand



Super-automatic espresso machine  
Brews 8 coffee varieties Integrated milk jug & frother, Stainless steel, 8 step adjustable grinder

HD8954/47

# Highlights

## Dual chamber milk carafe



Enjoy your milk specialties fully automated with the patented milk carafe with dual chamber technology. Simply pour milk into the carafe, plug it into the machine and select your coffee drink. With the dual chamber technology you will always enjoy professional coffee drinks with dense, long-lasting milk froth at the ideal temperature from a constant splash-free flow of milk.

## Auto cleaning and descaling



Saeco designed this espresso machine to automatically clean its coffee circuit with water upon starting up or switching off of the machine, this delivers a great, fresh taste with each cup of coffee. Regular descaling prolongs your espresso machine's life. This machine will not only prompt when descaling is needed, the automated descaling process will start on your machine and guides you with clear on-screen messages when you have to intervene. Descaling has never been so easy!

## Saeco adapting system 2



No matter the bean you use, Saeco's intelligent adapting system will optimize the grinding cycles for perfect brewing quantity of coffee.

## Crema and body boost



This Saeco features our patented crema and body boost. This dial, conveniently located at your machine's spout, allows you to smoothly adjust the counter pressure changing your espresso's body and crema. Try it yourself and find your favorite taste.

## Professional double boiler



With 2 separate heating systems to cater for both the optimal coffee or milk frothing

temperatures, this Saeco fully automatic espresso machine guarantees professional performance and speed everytime. You are able to prepare as many latte macchiatos and cappuccinos as you wish, one after the other and each just as good as the previous without waiting.

## 100% Ceramic grinders



Our grinders are made of high-tech ceramic: exceptionally hard and precise. Fresh beans are gently ground, without risk of overheating: extracting all the best flavors and aroma, delivering a superior coffee taste for at least 20,000 cups.

## Removable brewing group



Efficiency and ease of use were key inspirations when Saeco invented the first brewing group 30 years ago. And to this day, it still proves to be an inspired, resolute piece of technology. As always, it's so simple to clean – just remove it and wash it under the tap for a few seconds, then re-insert it just as easily.

Super-automatic espresso machine  
Brews 8 coffee varieties Integrated milk jug & frother, Stainless steel, 8 step adjustable grinder

HD8954/47

# Specifications

## Sustainability

- Power consumption brewing: 1500 W

## General specifications

- Cups at the same time: 2
- Suitable for: Whole coffee beans, ground coffee powder
- Type of carafe: Basic carafe
- Type of display: LCD
- Special functions: Ceramic grinder, Integrated carafe, Pre-brewing, Ground coffee option, Crema adjustment knob
- Customizing per drink: Adjustable coffee strength, Adjustable temperature, Adjustable cup volume, Adjustable milk foam amount
- Ease of use and comfort: Removable water tank, Display, Removable spout
- Ease of cleaning & maintenance: Automatic de-scaling cycle, Removable brewing group, Automatic carafe cleaning, Automatic rinse cycle
- Coffee drinks: Espresso, Cappuccino, hot water, Café Crème, frothed milk, Latte Macchiato, coffee, Ristretto, Americano, Caffèlatte

## Finishing

- Material boiler: Stainless steel (Inox)
- Material drip tray: Stainless steel

- Material of main body: Stainless steel
- Material water tank: Plastic

## Country of origin

- Made in: Italy

## Service

- 1-year guarantee

## Technical specifications

- Pump pressure: 15 bar
- Capacity milk carafe: 500 L
- Capacity bean container: 350 gr
- Capacity waste container: 14 servings
- Max. cup height: 150 mm
- Water boilers: 2
- Cord length: 0.8 m
- Capacity water tank: 1.6 L
- Frequency: 60 Hz
- Voltage: 120 V

## Weight and dimensions

- Weight of product: 16.1 kg
- Dimensions of product (WxDxH): 280 x 420 x 375 mm

## Design

- Color: Stainless steel

Issue date 2019-11-27

© 2019 Koninklijke Philips N.V.  
All Rights reserved.

Version: 4.0.1

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)