



**Saeco GranBaristo  
Super-automatic  
espresso machine**

- 18 Beverages
- Integrated milk carafe
- Stainless Steel
- AquaClean



HD8975/01

Enjoy a unique variety of 18 delicious specialties

Consistent result, exactly to your taste

The GranBaristo sets the standard in variety, comfort and indulgence thanks to a set of advanced technologies. And the patented VariPresso chamber can vary the brewing pressure to deliver an immense variety of quality drinks.

**Any coffee for any moment**

- Enjoy 18 beverages at your fingertips
- One-touch Cappuccino and Latte Macchiato with milk carafe
- Adjust the length, 6 aroma strength and 5 grinder settings
- Adjust and store up to 6 user profiles

**Every coffee crafted to perfection**

- 20,000 cups of finest coffee with durable ceramic grinders
- Perfect milk foam thanks to Latte Perfetto technology
- Variable brewing pressure for coffee and espresso
- Iconic stainless steel finishing, shaped to precision

**Attentive and anticipating at your command**

- Featuring AquaClean for up to 5000\* cups without descaling
- Clean milk residues after every use with milk clean function
- Enhanced control of your machine via the advanced display
- One-finger removable brewing group for an effortless clean

 **Saeco**

**PHILIPS**

Saeco, a Philips brand



# Highlights

## 18 beverages

Enjoy an unparalleled variety of drinks to suit any occasion. Whether you crave for an espresso, a coffee or a milk based recipe, your Super-automatic machine delivers a perfect in-cup result with no hassle and in no time!

## Integrated milk carafe



Enjoy super creamy cappuccino and Latte Macchiato at the perfect temperature, in the easiest way possible. Simply pour milk into the carafe, plug it into the machine, and select your preferred beverage. Whether it's a cappuccino or frothed milk, your drink will be served within seconds, with a splash-free flow at the ideal temperature.

## Customize your coffees



This Super-Automatic machine offers an abundance of indulgent options to customize your beverage to your taste. You can easily personalize and memorize length, strength and temperature for each drink. Feel free to explore, experiment and dream up any drink!

## User Profiles



Store your personal coffee settings in the easily accessible personal user profiles. You will be able to drink espresso, coffee, cappuccino and all other drinks always as you prefer, at the touch of a button.

## 100% ceramic grinders



Our grinders are made of high-tech ceramic: exceptionally hard and precise. Fresh beans are gently ground, without risk of overheating: extracting all the best flavors and aroma, delivering a superior coffee taste for at least 20,000 cups.

## Latte Perfetto Technology



Every coffee you prepare will be topped with a silky, milk layer that beckons the taste buds.

The milk carafe froths the milk twice, then pours a splash free creamy layer into your cup at just the right temperature. The carafe can also be stored conveniently in the fridge and it is incredibly hygienic.

## VariPresso Technology



The Saeco GranBaristo offers an unparalleled variety of drinks to suit any occasion thanks to the patented VariPresso brewing chamber. The secret is in the adjustable brewing pressure; set it on high for an intense, rich espresso, or lower the pressure for a long, classic coffee.

## Stainless steel finishing



Every minute detail of this machine was designed and crafted to the highest quality. The stainless steel finishing, inspired by Italian design and craftsmanship will stand the test of time in any classic or modern kitchen. An elegant vision of pure design, your machine will look as refined as the coffee it makes.

# Specifications

## General specifications

- Milk Solution: Integrated Milk Carafe, Quick Milk clean
- User Interface: Advanced display

## Technical specifications

- Capacity milk carafe: 0.5 L
- Capacity waste container: 20 servings
- Capacity water tank: 1.7 L
- Coffee bean capacity: 270 g
- Color & Finishing: Stainless Steel
- Cord length: >100 cm
- Country of origin: Italy
- Filter compatibility: AquaClean
- Frequency: 50 Hz
- Max. cup height: 165 mm
- Product dimensions: 205 x 360 x 460 mm
- Voltage: 230 V
- Waste container: Frontal access
- Water tank: Access from the top
- Weight of product: 13 kg

## Customization

- Aroma Strength Settings: 6
- Coffee and Milk Length: Adjustable
- Grinder Settings: 5
- Pre Brew Aroma control
- Temperature settings: 3
- User Profiles: 6

## Other features

- Auto-Rinse & Guided descaling
- Gusto perfetto
- Main Switch ON / OFF button
- Quick Heat Boiler
- Removable brew group

## Variety

- Beverages: Caffè crema, Cappuccino, Espresso, Espresso Double, Espresso Lungo, Espresso Macchiato, Flat White, Hot water, Latte Macchiato, Milk froth, Ristretto
- Coffee Powder Option
- Double Cup
- Milk Double Cup: No