

Bread maker

Daily Collection

12 menu

1000 g

White

13-hour delay timer



HD9015/30



## Wake up to fresh bread every day Bake any flavour. It's easy and delicious!

You will love the irresistible smell of fresh warm bread every morning! It's very simple.... Add your ingredients at night, set the delay timer for next morning, and let the Philips bread maker do the rest.

### **Bread just the way you like it**

- 12 pre-set programs to bake bread, make dough and even jam
- 3 browning levels for your preferred crust
- Up to 13-hour delay timer to wake up to freshly baked bread
- 'Add' indicator for specialty breads with extra ingredients
- Bake 2 sizes of loaf up to large 1kg

### **Great results with ease**

- Friendly design which is silent (< 65 dbA) and compact
- Handy recipe booklet included
- Measuring cup and spoon included
- Viewing window to let you watch bread rise and brown
- Detachable lid for easy cleaning

# Highlights

## 12 programs for bread and jam

The Philips breadmaker has 12 easy-to-use preset programs that bake any bread to perfection, from rich and satisfying whole wheat to gluten free, French and sweet varieties. It also makes delicious dough for pasta, even jams too. Whatever you bake, it's always delicious and easy to do because the pre-sets take care of the temperature and time for the best possible results. If you're in a hurry, you can use rapid program for quicker result, or even super rapid program that just bake in one hour only.

## 3 browning levels



Thanks to the advanced temperature control system, the Philips VIVA breadmaker lets you enjoy your bread just the way you like it, whether light, medium or dark crust, only with a simple push on the control panel.

## Up to 13-hour delay timer



Enjoy the irresistible smell of fresh warm bread every morning - a true treat and the perfect way to start the day! Simply set the delay timer the night before and the breadmaker will


prepare and bake your loaf while you sleep for freshly baked bread to eat the moment you wake up, or whenever you like.

## 'Add' ingredients indicator



During the mixing stage, the breadmaker will give 'beep' sounds to alert you to add other special ingredients to your specialty bread if you wish.

## Bake 2 sizes of loaf



Bake 2 sizes of loaf up to large 1kg

## Silent (< 65 dbA) and compact



The breadmaker has a very user friendly design which is silent (65dbA) when operating. Its compact design is superb to fit for any modern kitchen.

## Recipe booklet included



Handy recipe booklet included

## Detachable lid

Detachable lid for easy cleaning

## Viewing window



Viewing window to let you watch bread rise and brown

## Included with cup and spoon

Measuring cup and spoon included

# Specifications

**Accessories included**

Baking tin: Up to 1 kg  
Measuring cup  
Measuring spoon  
Paddle(s)

**Design specifications**

Color(s): Star white

**General specifications**

Add ingredients signal  
Bread capacity: 750gr, 1kg  
Browning levels: 3  
Cool wall exterior  
Dough program: Pasta, general (pizza, cookie, baguel, etc)  
Hours of delay timer: 13  
Jam program  
LCD display  
No. of paddles: 1  
No. of programs: 12

Non-slip feet

One-touch operation  
Rapid program  
Recipe booklet  
Warming period: 1 hour

**Material**

Baking tin: Aluminum alloy  
Main body: PP plastic  
Mixing paddle: Aluminum alloy

