

PHILIPS

Bread maker

Viva Collection

14 menu (incl. yoghurt)

1000 g

Black

13-hour delay timer



HD9046/90



Wake up to fresh bread every day

Bake any flavour. It's easy and delicious!

You will love the irresistible smell of fresh warm bread every morning! It's very simple... Add your ingredients at night, set the delay timer for next morning, and let the breadmaker do the rest.

Bread just the way you like it

- 14 pre-set programs for bread, dough, jam and even yoghurt
- 3 browning levels for your preferred crust
- Bake two sizes of loaf up to large 1kg
- Up to 13-hour delay timer to wake up to freshly baked bread
- 'Add' indicator for specialty breads with extra ingredients

Great results with ease

- Friendly design which is super silent (< 55 dbA) and compact
- Very comfortable control panel position for all users
- Handy recipe booklet included
- Measuring cup and spoon included
- Large viewing window to let you watch bread rise and brown

Enjoy your home made yoghurt

- Yoghurt container included

Highlights

14 programs for bread and jam




The Philips breadmaker has 14 easy-to-use preset programs that bake any bread to perfection, from rich and satisfying whole wheat to gluten free, French and sweet varieties. It also makes specialty breads such as Borodinsky, Easter bread and delicious dough for pasta, even jams too. Whatever you bake, it's always delicious and easy to do because the pre-sets take care of the temperature and time for the best possible results. If you're in a hurry, you can use rapid program for quicker result, or even super rapid program that just bake in one hour only.

3 browning levels



Thanks to the advanced temperature control system, the Philips VIVA breadmaker let you enjoy your bread just as the way you like it, whether light, medium or dark crust, only with a simple push on the control panel.

2 bread sizes for selection



Bake just the right amount of bread for your needs. Simply choose the loaf size on the control panel to bake medium (750g) or large (1000g) depending on your needs.

Up to 13-hour delay timer



Enjoy the irresistible smell of fresh warm bread every morning - a true treat and the perfect way to start the day! Simply set the delay timer the night before and the breadmaker will prepare and bake your loaf while you sleep for freshly baked bread to eat the moment you wake up, or whenever you like.

'Add' ingredients indicator



During the mixing stage, the breadmaker will give 'beep' sounds to alert you to add other special ingredients to your specialty bread if you wish.

Silent (< 55 dbA) and compact



The breadmaker has a very user friendly design which is super silent (55dbA) when operating, so wake you up with the smell of fresh bread, not by the noise. Its compact design is superb to fit for any modern kitchen.

Very comfortable control panel



Very comfortable control panel position for all users

Recipe booklet included



Handy recipe booklet included

Included with cup and spoon

Measuring cup and spoon included

Large viewing window

Large viewing window to let you watch bread rise and brown

Yoghurt making



Enjoy home made yoghurt using the special yoghurt program. The yoghurt container is included. Use the lid for easy storage.

Specifications

Accessories included

Baking tin: Up to 1 kg
Measuring cup
Measuring spoon
Paddle(s)
Yoghurt container with lid

Design specifications

Color(s): Black

General specifications

Add ingredients signal
Bread capacity: 750gr, 1kg
Browning levels: 3
Cool wall exterior
Dough program: Pasta, general (pizza, cookie, baguel, etc)
Hours of delay timer: 13
Jam program
LCD display
No. of paddles: 1
No. of programs: 14

Non-slip feet
One-touch operation
Rapid program
Recipe booklet
Warming period: 1 hour
Yoghurt program

Material

Baking tin: Aluminum alloy
Main body: PP plastic
Mixing paddle: Aluminum alloy

