

# PHILIPS

## Steamer

### Daily Collection

9 L, 900 W

Manual timer

Aroma Infuser, soup/rice bowl

Plastic, white/beige

HD9125/91



## Pure taste of steamed food

### With Aroma infuser

Steam with perfect settings for every meal.

#### **A healthy way to cook tasty meals**

- Aroma Infuser adds more taste with delicious herb & spices
- Healthy steaming keeps the nutrition in the food
- Food set timer for fish, vegetables, rice and more

#### **Easily cook a complete meal in one go**

- Egg rack
- Steaming bowl for soup, stew, rice and more
- 3 baskets to steam several ingredients at once
- 9L capacity and removable tray bottoms

#### **Smart and convenient handling**

- Anti drip lid
- Parts are dishwasher safe
- Easy to fill with water
- Stackable baskets for easy storage

# Highlights

## Aroma Infuser

The unique Aroma Infuser of the Philips steamer adds delicious aroma of herbs and spices, bringing even more taste to steaming. Simply pop your favourite herbs and spices into the booster, and let steam do the rest. The heat from the steam releases delicate aromas from the herbs and spices, which thoroughly infuse the food with their mouth-watering flavours.

## Healthy steaming

Healthy steaming keeps the nutrition in the food

## Food set timer

Food set timer for fish, vegetables, rice and more

## 3 baskets

3 baskets to steam different ingredients at the same time.

## 9L capacity

9L capacity and removable tray bottoms

## Egg rack

Fits 6 eggs per basket.

## Steaming bowl

Steaming bowl for soup, stew, rice and more

## Anti drip lid

Anti drip lid

## Dishwasher safe parts

Parts are dishwasher safe

## Easy waterfill

Easily refill the reservoir while in use.

## Stackable baskets

Stackable baskets for easy storage

# Specifications

## Accessories

Included: Egg rack, Rice/soup/food bowl

## Design and finishing

Color(s): White and beige

Material of main body: Plastic

## General specifications

Number of tiers: 3 pcs

Cool-touch handgrips

Cord storage

Non-slip feet

Overheat and dry boil protection

Power-on light

Water level indicator

## Technical specifications

Capacity watertank: 1 L

Cord length: 0.8 m

Frequency: 50/60 Hz

Power: 900 W

Voltage: 220-240 V

Capacity (max): 2.6 + 2.9 + 4.1

