

# PHILIPS

## Steamer

### Avance Collection

9 L, 900 W

Digital timer, heating turbo

Aroma Infuser, keep warm func.

Plastic, Black



HD9150/91



## The purest taste of steamed food

### Infuse your steamed food with herbs and spices

This high quality Philips steamer with unique Flavour Booster enriches the taste of steamed food with rich aroma of herbs and spices. Digital timer and keep warm function, all to help you prepare delicious meals every time.

#### **A healthy way to cook tasty meals**

- Aroma Infuser adds more taste with delicious herb & spices
- Keeps all the nutrients in your food during cooking
- Recipe booklet

#### **Easily cook a complete meal in one go**

- 9L capacity and removable tray bottoms
- Keep Warm function keeps food ready for serving

#### **Smart and convenient handling**

- Digital timer
- Easy to fill with water
- Digital water refill indicator with signal
- Parts are dishwasher safe

# Highlights

## Aroma Infuser



The unique Aroma Infuser of the Philips steamer adds delicious aroma of herbs and spices, bringing even more taste to steaming. Simply pop your favourite herbs and spices into the booster, and let steam do the rest. The heat from the steam releases delicate aromas from the herbs and spices, which thoroughly infuse the food with their mouth-watering flavours.

## 9L capacity



9L capacity and removable tray bottoms

## Digital timer



Digital timer signals when your food is ready.

## Digital Water refill indicator



Digital water refill indicator signals when water level is low.

## Easy waterfill



Easily refill the reservoir while in use.

## Keep Warm function




Keep Warm function keeps your food warm till it's served.

## Keeps all the nutrients

For an extra healthy lunch or evening meal, this steamer locks in nutrients to deliver supreme taste in no time at all.

## Recipe booklet



PHILIPS  
wakes and simplicity

Recipe booklet packed with expert tips and tasty treats.

## Dishwasher safe parts



Parts are dishwasher safe

# Specifications

## Design specifications

Material: Plastic

Color(s): Black

## Accessories included

Egg rack

## General specifications

Non-slip feet

Power-on light

Cool-touch handgrips

Water level indicator

Number of tiers: 3 pcs

Overheat and dry boil protection

Cord storage

## Technical specifications

Power: 900 W

Voltage: 220-240 V

Frequency: 50/60 Hz

Cord length: 100 cm

Capacity (max): 2.6/ 2.8/ 3.2 L

Capacity water tank: 1.1 L

