

PHILIPS

Plastic kettle

Series 3000

1.7 L

Spring lid

Light indicator

HD9318/00



Enjoy hot drinks in no time

Family-size 1.7L capacity, perfect for everyone

The new Philips plastic kettle with 1.7 L capacity, automatic lid opening and light indicator gives you the opportunity to easily make your favorite drink in no time.

Fast, safe boiling

- Flat heating element for fast boiling
- Micro-mesh filter captures tiny limescale particles
- Multi safety system against boil-dry

Simple to fill, use and clean

- Pilot light indicates when the kettle is switched on
- Easy-to-read water level indicator
- A cup indicator to boil only the water you need
- Spring lid with large opening for cleaning
- Easy refilling through lid or spout
- Cordless kettle with 360° pirouette base
- Cord winder for easy adjustment and storage

Highlights

Flat heating element



A concealed stainless steel heating element ensures fast boiling and easy cleaning.

Water level indicator



The water level is easy to read with an indicator located on one side of the kettle.

Easy refilling



The kettle can be filled through the spout or by opening the spring lid.

Micro-mesh filter



A removable micro-mesh filter on the spout captures tiny limescale particles as small as 200 microns to ensure a clear cup.

A cup indicator



Enabling consumers to boil the amount of water they need, and therefore saving up energy and water, contributing to a better environment.

Cordless + 360° pirouette base



The cordless kettle sits on a 360° pirouette base for easy lifting and replacing.

Multi safety system



Multi safety system against boil-dry, with auto-switch off when the water is ready.

Spring lid with large opening



A push-button lid opens smoothly at the touch of a button, avoiding steam contact. The large opening simplifies cleaning.

Hidden cord winder



The cord can be wrapped underneath the base, so it's the right length for any kitchen and easily stored away.

Pilot light



Elegant indicator light incorporated in the power switch illuminates when the kettle is turned on.

Specifications

General specifications

Product features: Lid and spout filling, Non-slip feet

Type of lid: Spring

Power-on light

On/off switch

Cord storage

Automatic shut-off

360 degrees base

Flat heating element

Design and finishing

Color(s): White

Material of main body: Plastic

Material filter: Nylon filter

Technical specifications

Capacity bowl: 1.7 L

Cord length: 0.75 m

Frequency: 50-60 Hz

Power: 1850-2200 W

Voltage: 220-240 V

Weight and dimensions

Weight of product: 0.89 kg

Weight incl. packaging: 1.22 kg

Dimensions of product (LxWxH):

160x223x253 mm

Dimensions of packaging (LxWxH):

190x226x250 mm

Micro mesh Filter

Country of origin

Made in: China

Service

2-year worldwide guarantee

Sustainability

Packaging: > 90% recycled materials

User manual: 100% recycled paper

