

# PHILIPS

Plastic kettle

Series 3000

1.7 L

Spring lid

Light indicator

HD9318/70



## Enjoy hot drinks in no time

Family-size 1.7L capacity, perfect for everyone

The new Philips plastic kettle with 1.7 L capacity, automatic lid opening and light indicator gives you the opportunity to easily make your favorite drink in no time.

### Fast, safe boiling

- Flat heating element for fast boiling
- Micro-mesh filter captures tiny limescale particles
- Multi safety system against boil-dry

### Simple to fill, use and clean

- Pilot light indicates when the kettle is switched on
- Easy-to-read water level indicator
- A cup indicator to boil only the water you need
- Spring lid with large opening for cleaning
- Easy refilling through lid or spout
- Cordless kettle with 360° pirouette base
- Cord winder for easy adjustment and storage

# Highlights

## Flat heating element



A concealed stainless steel heating element ensures fast boiling and easy cleaning.

## Water level indicator



The water level is easy to read with an indicator located on one side of the kettle.

## Easy refilling



The kettle can be filled through the spout or by opening the spring lid.

## Micro-mesh filter

A removable micro-mesh filter on the spout captures tiny limescale particles as small as 200 microns to ensure a clear cup.

## Multi safety system



Multi safety system against boil-dry, with auto-switch off when the water is ready.

## A cup indicator



Enabling consumers to boil the amount of water they need, and therefore saving up energy and water, contributing to a better environment.

## Cordless + 360° pirouette base



The cordless kettle sits on a 360° pirouette base for easy lifting and replacing.

## Pilot light



Elegant indicator light incorporated in the power switch illuminates when the kettle is turned on.

## Spring lid with large opening



A push-button lid opens smoothly at the touch of a button, avoiding steam contact. The large opening simplifies cleaning.

## Hidden cord winder



The cord can be wrapped underneath the base, so it's the right length for any kitchen and easily stored away.

# Specifications

## General specifications

**Product features:** Lid and spout filling, Non-slip feet

**Type of lid:** Spring

**Power-on light**

**On/off switch**

**Cord storage**

**Automatic shut-off**

**360 degrees base**

**Flat heating element**

## Design and finishing

**Color(s):** White

**Material of main body:** Plastic

**Material filter:** Nylon filter

## Technical specifications

**Capacity bowl:** 1.7 L

**Cord length:** 0.75 m

**Frequency:** 50-60 Hz

**Power:** 1850-2200 W

**Voltage:** 220-240 V

## Weight and dimensions

**Weight of product:** 0.89 kg

**Weight incl. packaging:** 1.22 kg

**Dimensions of product (LxWxH):**

160x223x253 mm

**Dimensions of packaging (LxWxH):**

190x226x250 mm

**Micro mesh Filter**

## Country of origin

**Made in:** China

## Service

**2-year worldwide guarantee**

## Sustainability

**Packaging:** > 90% recycled materials

**User manual:** 100% recycled paper

