

PHILIPS

Kettle

Avance Collection

1.5 litre

2200 W

With glass jug



HD9340/90



Extra robust, long-lasting glass

The first glass kettle from Philips combined with stainless steel material gives you extra robust and long-lasting quality. Cup-by-cup indication lets you boil just what you need and therefore contributes to a better environment.

Easy to experience

- Pilot light indicates when the kettle is switched on
- Power cord winder for easy storage
- Cordless 360° pirouette base for easy lifting and placing.
- Hinged lid with release button for easy filling and cleaning
- One cup indicator to boil only the water you need

Fast boiling and easy cleaning

- Flat heating element for fast boiling and easy cleaning
- Anti-limescale filter for a clear cup of water

Safe to use

- Multi safety system

Robust and long-lasting

- SCHOTT DURAN® glass made in Germany is perfect for boiling



asimpleswitch.com

Highlights

Power cord winder



The cord can be wrapped around the base, so that the kettle is easy to place in your kitchen.

Pilot light



Elegant light incorporated in the on/off switch indicates when the kettle is on.

Flat heating element

The stainless steel concealed element ensures fast boiling and easy cleaning.

One cup indicator



Enabling consumers to boil the amount of water they need, and therefore saving up energy and water, contributing to a better environment.

Cordless 360° pirouette base



Cordless 360° pirouette base for easy lifting and placing.

Hinged lid with release button

Hinged lid with release button for easy filling and cleaning, also avoiding steam contact.

SCHOTT DURAN® glass



The kettle body is made from special glass by SCHOTT DURAN® in Germany that is extra robust, long-lasting and best for high-temperature applications like boiling.

Multi safety system

Multi safety system against boil-dry, with auto switch-off when ready

Anti-limescale filter



The removable anti-limescale filter ensures the water you pour into your cup is clean.

Specifications

Design specifications

Heating element: Stainless steel
Material switch: Polypropylene (PP)
Colour(s): White and black

General specifications

Cordless
Non-slip feet
Ergonomic grip
Wide opening lid
Cord storage
Automatic shut-off
Boil-dry protection
360-degree base
Flat heating element

Accessories

Filter: Spout filter

Technical specifications

Capacity: 1.5 L
Cord length: 0.75 m
Frequency: 50/60 Hz
Power: 1850 - 2200 W
Voltage: 220-240 V

Service

2-year worldwide guarantee



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas — Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.