

PHILIPS

Kettle

Avance Collection

1.5 L 2200 W

SCHOTT DURAN® glass

Water level indicator

Spring lid



HD9342/01



Extra robust, long-lasting glass

The first glass kettle from Philips combined with stainless steel material gives you extra robust and long-lasting quality. Cup by cup indication lets you boil just what you need and therefore contributing to a better environment.

Easy to experience

- Pilot light indicates when the kettle is switched on
- Power cord winder for easy storage
- Cordless 360° pirouette base for easy lifting and placing.
- Easy to read water level indicators on both sides
- Hinge lid with release button for easy filling and cleaning
- One cup indicator to boil only the water you need

Fast boiling and easy cleaning

- Flat heating element for fast boiling and easy cleaning
- Anti-limescale filter for a clear cup of water

Safe to use

- Multi safety system

Robust and long-lasting

- SCHOTT DURAN® glass made in Germany is perfect for boiling



asimpleswitch.com

Highlights

Power cord winder



The cord can be wrapped around the base, so that the kettle is easy to place in your kitchen.

Multi safety system

Multi safety system against boil-dry, with auto switch off when ready

Pilot light



Elegant light incorporated in the on/off switch indicates when the kettle is on.

Flat heating element

The stainless steel concealed element ensures fast boiling and easy cleaning.

One cup indicator



Enabling consumers to boil the amount of water they need, and therefore saving up energy and water, contributing to a better environment.

Cordless 360° pirouette base



Cordless 360° pirouette base for easy lifting and placing.

Easy water level indicator



Easy to read water level indicators on both sides

Hinge lid with release button



Hinged lid with release button for easy filling and cleaning, also avoiding steam contact.

SCHOTT DURAN® glass



The kettle body is made of special glass by SCHOTT DURAN® in Germany which is extra robust, long-lasting and best for high temperature application like boiling.

Anti-limescale filter



The removable anti-limescale filter ensures the water you pour into your cup is clean.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Design specifications

Heating element: Stainless steel
Material switch: Polypropylene (PP)
Color(s): Stainless Metal & black

General specifications

Cordless
Non slip feet
Ergonomic grip
Wide opening lid

Cord storage
Automatic shut-off
Boil-dry protection
360 degrees base
Flat heating element

Accessories

Filter: Spout filter

Technical specifications

Capacity: 1.5 L
Cord length: 0.75 m
Frequency: 50/60 Hz
Power: 1850 - 2200 W
Voltage: 220-240 V

Service

2-year worldwide guarantee

