

PHILIPS

Kettle

Daily Collection

Metal

Spring lid

Light indicator

1.7 L

HD9352/50



Designed to last

Full stainless steel with extra-large lid opening

Durable kettle in safe, food-grade full stainless steel for long and reliable daily use. Philips brings 60 years of trust and expertise to this elegant long-life kettle.

Fast, safe boiling

- Flat heating element for fast boiling
- Micro-mesh filter captures tiny limescale particles
- Multi safety system against boil-dry
- Durable full stainless steel body for long life

Simple to fill, use and clean

- Cord winder for easy adjustment and storage
- Cordless kettle with 360° pirouette base
- Easy refilling through lid or spout
- Easy-to-read water level indicator
- Spring lid with large opening for cleaning
- Pilot light indicates when the kettle is switched on

Highlights

Hidden cord winder



The cord can be wrapped underneath the base, so it's the right length for any kitchen and easily stored away.

Flat heating element



A concealed stainless steel heating element ensures fast boiling and easy cleaning.

Spring lid with large opening*



A push-button lid opens smoothly at the touch of a button, avoiding steam contact. The large opening simplifies cleaning.

Cordless + 360° pirouette base



The cordless kettle sits on a 360° pirouette base for easy lifting and replacing.

Micro-mesh filter



A removable micro-mesh filter on the spout captures tiny limescale particles as small as 200 microns to ensure a clear cup.

Pilot light



Elegant indicator light incorporated in the power switch illuminates when the kettle is turned on.

Easy refilling



The kettle can be filled through the spout or by opening the spring lid.

Multi safety system



Multi safety system against boil-dry, with auto-switch off when the water is ready.

Stainless steel design



Durable full-metal design in food-grade brushed stainless steel for long, reliable use.

Water level indicator



The water level is easy to read with an indicator located underneath the handle.

Specifications

General specifications

Product features: 360 degrees base, Automatic shut-off, Boil-dry protection, Cord storage, Flat heating element, Non-slip feet, On/off switch, Pilot light, Spring lid, Wide opening lid

Cordless

Easy spout filling

Ergonomic grip

Lid as well as spout filling

Spring lid opening

Service

2-year worldwide guarantee

Sustainability

Packaging: > 90% recycled materials

User manual: 100% recycled paper

Technical specifications

Cord length: 0.75 m

Frequency: 50/60 Hz

Power: 1850–2200 W

Voltage: 220–240 V

Capacity: 1.7 L

Weight and dimensions

Micromesh filter: 200 µm

Design

Color: Champagne

Finishing

Material of main body: Stainless steel

Material power switch: Polypropylene (PP)

