

PHILIPS

Kettle

Avance Collection

1.0 L 2400 W

Digital temp control

Ink black

Spring lid

HD9380/21



Great tasting hot drinks

With optimal temperature settings for your drink

Looking for the optimal taste for your drink? To get the maximum flavour, every hot drink should be made at an ideal temperature. By choosing the right temperature icon on your kettle, you can now enjoy the optimal taste of your hot drink.

Great tasting hot drinks

- Keep warm function keeps the water at your set temperature
- 5 pre-set buttons for selection of your preferred hot drink

Fast boiling and easy cleaning

- One cup indicator to boil only the water you need
- Spout filter for a cleaner cup and kettle
- Flat heating element for fast boiling and easy cleaning

Easy to experience

- Cordless 360° pirouette base for easy lifting and placing
- Easy lid and spout filling

Safe to use

- Multi safety system

Highlights

Keep warm function



You do not need to re-boil your water continuously anymore. The keep warm function ensures that the water is kept warm at the right temperature for the selected preset.

Easy lid and spout filling



The kettle can be filled via the spout or by opening the hinged lid.

Cordless 360° pirouette base



Cordless 360° pirouette base for easy lifting and placing.

Spout filter




The fine micro-mesh filter on the spout ensures that the water you pour into your cup is clean and no calc particles end up in your drink.

One cup indicator



Enabling consumers to boil the amount of water they need, and therefore saving up energy and water, contributing to a better environment.

Flat heating element



The stainless steel concealed element ensures fast boiling and easy cleaning.

Multi safety system



Multi safety system against boil-dry, with auto switch off when ready

5 pre-set hot drink buttons



The pre-set temperature settings of 40, 80, 90, 95 and 100°C will ensure that the basic ingredient for your tea, instant coffee, soup or noodles is at the temperature you like.

Specifications

Design specifications

Color(s): Ink black
Heating element: Stainless steel

General specifications

Cordless
Ergonomic grip
Wide opening lid
Automatic shut-off
360 degrees base
Boil-dry protection

Cord storage
Flat heating element
Lid as well as spout filling

Accessories

Filter: Single filter

Technical specifications

Capacity: 1.0 L
Power: 2400 W

Dimensions

Product dimensions (WxDxH): 20 x 22 x 23 cm
Packaging dimensions (WxDxH): 32,6 x 29,5 x 23,6 cm

Service

2-year worldwide guarantee

