

# PHILIPS

## Kettle

Avance Collection

1.7 L 2400 W

Digital temp control

Ink black

Spring lid



HD9384/20



## Great tasting hot drinks

With optimal temperature settings for your drink

Looking for the optimal taste for your drink? To get the maximum flavour, every hot drink should be made at an ideal temperature. By choosing the right temperature icon on your kettle, you can now enjoy the optimal taste of your hot drink.

### Great tasting hot drinks

- 5 pre-set buttons for selection of your preferred hot drink
- Keep warm function keeps the water at your set temperature

### Fast boiling and easy cleaning

- One cup indicator to boil only the water you need
- Flat heating element for fast boiling and easy cleaning
- Spout filter for a cleaner cup and kettle

### Easy to experience

- Easy lid and spout filling
- Cordless 360° pirouette base

### Safe to use

- Multi safety system

# Highlights

## 5 pre-set hot drink buttons



The pre-set temperature settings of 40, 80, 90, 95 and 100°C will ensure that the basic ingredient for your tea, instant coffee, soup or noodles is at the temperature you like.

## Keep warm function



You do not need to re-boil your water continuously anymore. The keep warm function ensures that the water is kept warm at the right temperature for the selected preset.

## Easy lid and spout filling



The kettle can be filled via the spout or by opening the lid.

## One cup indicator



Enabling consumers to boil the amount of water they need, and therefore saving up energy and water, contributing to a better environment.

## Flat heating element



The stainless steel concealed element ensures fast boiling and easy cleaning.

## Cordless 360° pirouette base



Cordless 360° pirouette base for easy lifting and placing.

## Multi safety system



Multi safety system against short circuit and boil-dry, with auto switch off when ready or when lifted from the base.

## Spout filter



The fine micro-mesh filter on the spout ensures that the water you pour into your cup is clean and no calc particles end up in your drink.

# Specifications

**Accessories**

**Included:** Spout filter

**General specifications**

**Product features:** 360 degrees base, Automatic shut-off, Boil-dry protection, Cord storage, Flat heating element, Ergonomic grip, Lid and spout filling, Wide opening lid

**Service**

2-year worldwide guarantee

**Technical specifications**

**Capacity:** 1.7 l

**Power:** 2400 W

**Weight and dimensions**

**Dimensions of packaging (LxWxH):** 236 x 356 x 236 mm

**Dimensions of product (LxWxH):** 200 x 270 x 230 mm

**Design**

**Color:** Ink Black

**Finishing**

**Material heating element:** Stainless steel

