

PHILIPS

Airfryer XXL

Premium

Smart Sensing technology

Fat Removal technology

Rapid Air Technology

Black, copper, 1.4kg



HD9860/91



Maximum taste, minimum fat. Effortlessly. Perfect results at the touch of a button

The new Philips Airfryer XXL does the thinking and cooking for you. With Smart Sensing technology, it is the only Airfryer that automatically adjusts time and temperature during cooking for perfectly cooked dishes. Select and enjoy every bite!

Best Philips Airfryer ever made

- Hundreds of recipes in app and free recipe book included
- The only Airfryer with Fat removal technology
- The original Airfryer with 7 times faster airflow*
- Versatile: Fry. Bake. Grill. Roast. And even reheat!
- XXL capacity, cooks a whole chicken or 1.4kg of fries

Ideal for your daily cooking

- Convenient Keep Warm mode
- Cooks meals 1.5 times faster than an oven**
- QuickClean and dishwasher-safe for all removable parts

Perfect results at the touch of a button

- Convenient "Save your favorite" cooking setting
- Smart Chef programs for popular dishes
- Smart Sensing technology

Highlights

Smart Sensing technology



The new generation of Philips Airfryer does the thinking for you. Enjoy perfect results in two easy steps. Choose a food type and press the button to cook. Smart sensor automatically adjusts the time and temperature for effortless perfect results. Every time!

Smart chef programs



Our professional chefs designed the Smart Chef programs to do the thinking and cooking for you. Fresh or frozen fries, drumsticks or a whole chicken and even a whole fish—with just one touch, your Airfryer XXL will do the thinking and cooking for you.

Save your favorite meal



You can save your favorite dish and it will make it just the way you like, every time. And at the touch of one button. The favorite mode will cook your meal for the perfect time and temperature for ultimate convenience. Whether it's a delicious hot breakfast or favorite family recipe, it's perfect every time.

Rapid Air for 90% less fat



Enjoy healthier fried food that's crispy on the outside and tender on the inside with up to 90% less fat*. The Philips Airfryer XXL uses hot air (instead of oil) to fry food with little to no added oil. Philips Rapid Air creates 7x faster airflow so that you can enjoy crispier results* and delicious taste.

Remove excess fat from food



Now you can eat healthier dishes and remove the excess fat from food. Phillips XXL is the only Airfryer with Fat Removal technology that separates and captures excess fat. Savor all the taste of a roasted whole chicken with crispy skin, tender meat and up to 50% less saturated fat****.

XXL Family size meals



Yes, you can cook family-size meals in the new Airfryer XXL. It's full-size capacity makes cooking a large, delicious meal easy. You can cook a whole chicken or even up to 1.4 kg of fries to satisfy hungry family or friends. Cook up to six portions with the large 7.3L capacity basket.

Bake. Grill. Roast. Or reheat.



You can make hundreds of dishes in your Airfryer XXL. Fry, bake, grill, roast and even reheat your meals. Every bite is as delicious as the last thanks to Philips Air flow and the starfish design. It cooks food uniformly from all sides for perfect meals every time.

Exclusive NutriU app



You can be inspired to become a master Airfryer chef. With the purchase of your new Philips Airfryer XXL you get exclusive access to our NutriU app. Browse hundreds of delicious recipes. And try out even more tasty dishes with your complimentary Phillips Airfryer Recipe Book.

QuickClean and dishwasher-safe



Clean-up is fast and easy thanks to the Airfryer QuickClean basket with removable, non-stick mesh insert. All the removable parts are dishwasher-safe for no-fuss cleaning.

Specifications

Accessories

Included: Recipe booklet

Country of origin

Made in: China

General specifications

Product features: Automatic shut-off, Cool wall exterior, Dishwasher safe, On/off switch, Ready signal, Temperature control, Power-on light, Quickclean, Cancel button, Integrated cord storage, LED display, Patented Rapid Air, Preset cooking function, Time control

Prefix programs: 5

Keep warm function: 30 min

Service

2-year worldwide guarantee

Sustainability

Packaging: > 90% recycled materials

User manual: 100% recycled paper

Technical specifications

Cord length: 0.8 m

Power: 2200-2225 W

Voltage: 220-240 V

Frequency: 50/60 Hz

Weight and dimensions

Dimensions of product (LxWxH):

433.10x321.60x315.70 mm

Weight of product: 7.99 kg

Design and finishing

Color of control panel: Black

Color(s): Deep black with copper

Material of main body: Plastic

