




PHILIPS



HI 240/42/44



PHILIPS

STEAM BOOST

MISTRAL 40 HI 240
MISTRAL 42 HI 242
MISTRAL 44 HI 244

The new steam iron from Philips provides a convenient way to iron. It has a good steam performance and all the controls for steam and temperature placed in front for easy reach and manoeuvring. Introducing an impressive steam boost to remove even the most stubborn wrinkles. This iron is designed for use with tap water (up to 17°C) and has excellent suppression of radio or TV interference. A thermal fuse is integrated to ensure no hazardous melting or burning.

Mistral 40/42/44 is packed in an attractive carton box. All materials used are environmentally friendly.

FEATURES

- Steam Boost
- Front Control
- Variable Steam (upto 15 gr/min)
- Spray
- Transparent Water Tank (approx. 200 ml)
- Self Clean
- Pilot lamp
- Flexible Cord (with moulded plug and swivel)
- Cordwinder
- 35 large steam vents

OPTIONS

- Mistral 40 (HI 240) is provided with an aluminium soleplate
- Mistral 42 (HI 242) is provided with a silverstone soleplate
- Mistral 44 (HI 244) is provided with a stainless steel soleplate

TECHNICAL DATA

- Power : 1200/1325/1450W, 1200W
- Voltage : 220/230/240V, 120V
- Frequentie : 50/60Hz
- Cord : 2m, cotton braided
- Dimensions : 28.7 (L) x 11.4 (W) x 14.3 (H) cm
- Weight : 1.35 Kg

PACKAGING

- Dimension F-box : 31.3 (L) x 12.6 (W) x 15.5 (H) cm
- Weight : 1.60 Kg
- Dimension A-box : 49.9 (L) x 28.6 (W) x 35.5 (H) cm
- Weight : 10.5 Kg
- A-box Qty : 6 pcs
- Pallet Qty : 288 pcs

Product specification is subject to change without prior notice.