

# PHILIPS

## Steam generator iron

Max 5 bar pump pressure

1.1L detachable water tank

180 g steam boost



HI5914/36



## Faster ironing

### With extra steam

This steam generator makes your ironing experience faster thanks to extra powerful continuous steam and more convenient thanks to a 1.1L detachable water tank.

#### Compact & convenient

- 1.1L detachable water tank
- Lightweight and compact for easy use and storage

#### Fast & powerful

- Calc-clean container included — no cartridges, no extra cost
- Ceramic soleplate for durability and easy gliding
- Powerful steam for ultimate crease removal

# Highlights

## Detachable 1,1L water tank



The watertank can be removed to be refilled easily under the tap. The large filling hole makes the refilling fast. Thanks to the 1.1 L watertank capacity, you can iron up to 2 hours continuously without any refills.

## Smart descaling



Our built in descaling system, Smart Calc Clean reminds you when you need to descale. It includes a container to make descaling easy. This means no cartridges are required and no additional costs.

## Ultra-powerful steam



Strong, continuous steam tackles even the thickest fabrics with ease. Watch stubborn creases melt away with an extra steam boost

just where you need it. This extra steam is perfect for vertical steaming to refresh clothes and curtains, too.

## Compact and convenient



The lightweight, compact size is perfect for storage and fits conveniently on your ironing board. Exclusive ProVelocity technology makes our steam generators smaller and more compact than ever.

## Ceramic soleplate



Our durable ceramic soleplate glides well on all garments. It's non-stick, scratch-resistant and simple to keep clean.

# Specifications

## Fast crease removal

**Continuous steam:** up to 100 g/min

**Power:** 2400 W

**Pressure:** max 5 bar pump pressure

**Steam boost:** 180 g

**Vertical steam**

**Voltage:** 220-240 V

## Easy to use

**Soleplate name:** Ceramic

**Water tank capacity:** 1100 ml

**Detachable water tank**

**Hose length:** 1.6 m

**Power cord length:** 1.6 m

**Refill any time during use**

**Tap water suitable**

**Extra large filling hole**

## Scale management

**Descaling and cleaning:** Smart Calc Clean

**Descaling reminder:** Yes, no cartridges needed, no extra

## Accessories included

Calc clean container

## Size and weight

**Product dimensions (WxHxL):**

36.2x27x26.3 cm

**Weight of iron:** 1.1 kg

**Weight of iron + base:** 3.2 kg

## Guarantee

2 year worldwide guarantee

## Technical specifications

**Heating time:** 2 min.

