

# PHILIPS

## Steam generator iron

Max 5.2 bar pump pressure

Detachable water tank



HI5915/35



## Faster ironing

### With extra steam

This steam generator makes your ironing experience faster and more convenient.

#### Convenient

- 1.1L detachable water tank
- Intelligent calc clean reminder with sound & light
- Tap water friendly, refill anytime during ironing

#### Faster ironing

- Ceramic Soleplate
- Continuous steam up to 100 g/min

# Highlights

## Detachable 1,1L water tank



The watertank can be removed to be refilled easily under the tap. The large filling hole makes the refilling fast. Thanks to the 1.1 L watertank capacity, you can iron up to 2 hours continuously without any refills.

## Smart Calc Clean



Smart Calc Clean is an integrated descaling and cleaning function to protect your appliance. To ensure an optimal steam performance, long lasting life and in order to prevent white flakes, your steam generator iron will remind you to perform the descaling process. For maximum convenience make sure to always use the Smart Calc Clean container provided with your appliance.

## Continuous steam



The more steam, the faster the ironing. The unique technology used in a Philips steam generator iron generates powerful steam making ironing easier, better and faster.

## Refill tap water any time



Your steam generator iron is designed to use tap water. While ironing, when you run out of water in the watertank, you can refill it easily without waiting or turning your appliance off.

## Ceramic Soleplate



Our Easy Gliding soleplate for all ironable garments and high scratch resistance.

# Specifications

## Fast crease removal

Continuous steam: up to 100 g/min  
 Power: 2400 W  
 Pressure: max 5,2 bar pump pressure  
 Steam boost: 200 g  
 Vertical steam  
 Voltage: 220-240 V

## Easy to use

Soleplate name: Ceramic  
 Water tank capacity: 1100 ml  
 Detachable water tank  
 Hose length: 1.4 m  
 Power cord length: 1.6 m  
 Refill any time during use  
 Tap water suitable  
 Extra large filling hole

## Scale management

Descaling and cleaning: Smart Calc Clean  
 Descaling reminder

## Accessories included

Calc clean container

## Size and weight

Product dimensions (WxHxL): 36.2x27x26.3 cm  
 Weight of iron: 1.1 kg  
 Weight of iron + base: 3.2 kg

## Guarantee

2 year worldwide guarantee

## Technical specifications

Heating time: 2 min.

