

PHILIPS

Steam generator iron


Max 5 bar pump pressure

1.1-l detachable water tank

180 g steam boost



HI5916/26



Faster ironing

With extra steam

This steam generator makes your ironing experience faster thanks to extra powerful continuous steam, and more convenient thanks to a 1.1 L detachable water tank.

Compact and convenient

- 1.1-l detachable water tank
- Lightweight and compact for easy use and storage

Fast and powerful

- Calc-clean container included — no cartridges, no extra cost
- Ceramic soleplate for durability and easy gliding
- Powerful steam for ultimate crease removal

Highlights

Detachable 1.1 l water tank



The water tank can be removed to be refilled easily under the tap. The large filling hole makes refilling fast. Thanks to the 1.1-l water tank capacity, you can iron for up to 2 hours continuously without any refills.

Smart descaling



Our built-in descaling system, Smart Calc Clean, reminds you when you need to descale. It also includes a container to make descaling easy. This means no cartridges are required and there are no additional costs.


Ultra-powerful steam



Strong, continuous steam tackles even the thickest fabrics with ease. Watch stubborn creases melt away with an extra steam boost

just where you need it. This extra steam is perfect for vertical steaming to refresh clothes and curtains, too.

Compact and convenient



The lightweight, compact size is perfect for storage and fits conveniently on your ironing board. Exclusive ProVelocity technology makes our steam generators smaller and more compact than ever.

Ceramic soleplate



Our durable ceramic soleplate glides well on all garments. It is non-stick, scratch-resistant and simple to keep clean.

Specifications

Fast crease removal

Continuous steam: up to 100 g/min

Power: 2400 W

Pressure: max 5 bar pump pressure

Steam boost: 180 g

Vertical steam

Voltage: 220–240 V

Easy to use

Soleplate name: Ceramic

Water tank capacity: 1100 ml

Detachable water tank

Hose length: 1.6 m

Power cord length: 1.6 m

Refill anytime during use

Tap water suitable

Extra-large filling hole

Scale management

Descaling and cleaning: Smart Calc Clean

Descaling reminder: Yes, no cartridges needed, no extra

Accessories included

Calc clean container

Size and weight

Product dimensions (W x H x D): 36.2 x 27 x 26.3 cm

Weight of iron: 1.1 kg

Weight of iron + base: 3.2 kg

Guarantee

2 year worldwide guarantee

Technical specifications

Heating time: 2 min.

