

PHILIPS

Steam generator iron


Max 5 bar pump pressure

1.1L detachable water tank

180 g steam boost



HI5917/20



Faster ironing

With extra steam

This steam generator makes your ironing experience faster thanks to extra powerful continuous steam and more convenient thanks to a 1.1L detachable water tank.

Comfortable ironing

- Automatic shut-off when the iron is left unattended

Compact & convenient


- Lightweight and compact for easy use and storage
- 1.1L detachable water tank

Fast & powerful

- Calc-clean container included — no cartridges, no extra cost
- Ceramic soleplate for durability and easy gliding
- Powerful steam for ultimate crease removal

Highlights

Auto shut-off



The iron shuts itself off if you leave it standing still. On its soleplate, it will automatically switch off after 30 seconds. On its heel rest, it will automatically switch off after 8 minutes.

Smart descaling



Our built in descaling system, Smart Calc Clean reminds you when you need to descale. It includes a container to make descaling easy. This means no cartridges are required and no additional costs.

Ceramic soleplate



Our durable ceramic soleplate glides well on all garments. It's non-stick, scratch-resistant and simple to keep clean.

Compact and convenient



The lightweight, compact size is perfect for storage and fits conveniently on your ironing board. Exclusive ProVelocity technology makes our steam generators smaller and more compact than ever.

Ultra-powerful steam



Strong, continuous steam tackles even the thickest fabrics with ease. Watch stubborn creases melt away with an extra steam boost just where you need it. This extra steam is perfect for vertical steaming to refresh clothes and curtains, too.

Detachable 1,1L water tank



The watertank can be removed to be refilled easily under the tap. The large filling hole makes the refilling fast. Thanks to the 1.1 L watertank capacity, you can iron up to 2 hours continuously without any refills.

Specifications

Fast crease removal

Continuous steam: up to 100 g/min
 Power: 2400 W
 Pressure: max 5 bar pump pressure
 Steam boost: 180 g
 Vertical steam
 Voltage: 220-240 V

Easy to use

Soleplate name: Ceramic
 Water tank capacity: 1100 ml
 Detachable water tank
 Hose length: 1.4 m
 Power cord length: 1.6 m
 Refill any time during use
 Tap water suitable
 Extra large filling hole
 Auto shut-off

Scale management

Descaling and cleaning: Smart Calc Clean
 Descaling reminder: Yes, no cartridges needed, no extra

Accessories included

Calc clean container

Size and weight

Product dimensions (WxHxL): 36.2x27x26.3 cm
 Packaging dimensions (WxHxL): 39x23x27 cm
 Total weight with packaging: 3.5 kg
 Weight of iron: 1.1 kg
 Weight of iron + base: 3.2 kg

Guarantee

2 year worldwide guarantee

Technical specifications

Heating time: 2 min.

Green efficiency

Product packaging: 99% recyclable & 99% recycled
 User manual: >75% recycled

