

PHILIPS

Steam generator
iron

FastCare

Max 5.5 bar pump pressure

260 g steam boost

Carry lock

2.2 L detachable watertank



HI7716/20



Fast and convenient ironing

With detachable water tank

A large detachable water tank for easy refill, strong steam boost and the SteamGlide Ceramic soleplate will help you reducing your ironing time significantly while carry lock and Smart CalcClean make ironing convenient.

Maximum convenience

- 2,2L XL detachable water tank, ideal for families
- Carry lock for easy and safe transportation
- Refill tap water anytime
- Intelligent calc clean reminder with sound & light

Fast ironing

- Max 5.5 bar pump pressure
- Ready to use in 2 minutes with unlimited refill
- Smooth and easy gliding with Steam Glide Ceramic soleplate
- Continuous steam
- Steam boost up to 260 g

Highlights

2,2 L detachable water tank



A large detachable water tank for easy refill, strong steam boost and the SteamGlide Ceramic soleplate will help you reducing your ironing time significantly while carry lock and Smart CalcClean make ironing convenient

Safe Carry Lock

Your steam generator iron comes with a safety carry lock. You can lock your iron safely on the base, making it safer and reducing the risk of people touching the hot soleplate. You can also carry the steam generator easily.

Refill tap water anytime



Your steam generator iron is designed to use tap water. While ironing, when you run out of water in the watertank, you can refill it easily without waiting or turning your appliance off.

Smart Calc Clean

Smart Calc Clean is an integrated descaling and cleaning function to protect your appliance. To ensure an optimal steam

performance, long lasting life and in order to prevent white flakes, your steam generator iron will remind you to perform the descaling process. For maximum convenience make sure to always use the Smart Calc Clean container provided with your appliance.

Max 5,5 bar pump pressure

The more steam, the faster the ironing. Consistent powerful steam is generated which penetrates deep inside the garments making ironing faster and better. Steam power can be regulated to fit your needs.

Ready to use in 2 minutes

Steam is ready to use in 2min and can be refilled at anytime during ironing.

SteamGlide Ceramic soleplate

SteamGlide Ceramic combines good gliding and scratch resistance to help in smooth ironing

Continuous steam

The more steam, the faster the ironing. The unique technology used in a Philips steam generator iron generates powerful steam making ironing easier, better and faster.

Steam boost up to 260 g



The steam boost can be used for vertical steaming and tough creases.

Specifications

Accessories

Calc Clean container

Calc management

Calc clean reminder

Calc clean solution: Smart Calc Clean

Filtered water recommended

Suitable for tap water

Easy to use

Cord freedom (swivel): 180 degree cord freedom

Cord storage: Cord storage compartment

Heat up time: 2 min

Hose storage: Hose storage compartment

Power cord length: 1.6 m

Refill any time

Safety auto off

Storage solution: Carry lock

Water tank capacity: 2200 ml

Filling and emptying water: Extra large filling hole

Fast & powerful crease removal

Continuous steam output: 120 g/min

Power: 2400 W

Soleplate: SteamGlide Ceramic

Steam boost: 260 g

Vertical steaming

Pressure: 5.5

Sustainability

User manual: 100% recycled paper

Technical specifications

Voltage: 220 - 240 V

Service

2-year worldwide guarantee

Design

Color: Black purple

