

# PHILIPS

Infrared lamp

150W



HP3616



## Relieves muscular pains and common colds

### Deep, focused warmth

Philips infrared lamp gives pain relief for muscles and joints. Its 150 W infrared warmth penetrates deep into skin, improving blood circulation thereby giving relief for areas of 20x30 cm. Concentric rings help to focus on specific spots.

#### **Relieves muscle pain and colds**

- Deep penetrating Infrared warmth

#### **Extra focused treatment**

- 150 Watt infrared lamp with extra focus

#### **Easy to use**

- Adjustable angle
- On/off switch

#### **Easy to store**

- Cord storage

#### **Philips - the light expert**

- More than 15 million infrared lamps sold

# Highlights

## Deep penetrating Infrared warmth



Infrared light has been proven to effectively relieve aches and pains caused by muscular pains and stiff joints. The comfortable warmth created by infrared light penetrates deep into your skin, increasing blood circulation and warming your muscles. As your muscles are soothed, they automatically loosen up and relax. At the same time, the increased blood circulation helps your body get rid of impurities and quickly sends oxygen-rich blood to stressed or aching muscles, bringing effective pain relief.

## 150 Watt infrared lamp with extra focus



# 150W

The Philips Infrared lamp has been optimised for relief of pains in areas covering 20 x 30 cm, such as a shoulder, an elbow, a calf, or the

neck and for relief of common colds. The 150 Watt infrared lamp radiates 50% more comfortable warmth. The concentric rings help to focus the beams on a specific area.

### Adjustable angle

The appliance can easily be positioned upto 40 degrees backwards.

### On/off switch

Easy on/off switch at the back of the appliance, so the appliance does not have to be unplugged after each treatment.

### Cord storage

The appliance has a cord storage holder at the back of the appliance. Simply wrap the cord around it and it can easily be stored again.

### Philips - the light expert

Philips is one of the global leading companies in light, with over 100 years of light experience. Globally Philips already sold more than 15 million of Infrared lamps.

# Specifications

## Easy storage

### Cord storage

## Technical specifications

Power: 150 W

Voltage: 220/230 or 240/250V V

Frequency: 50 Hz

Cord length: 1.8 cm

Insulation: Class II (double isolation)

Type of lamps: PAR 38E, 150 W + prismatic rings for more focus

Lifetime of lamp: 750 sessions of 10 minutes

## Weight and dimensions

Product dimensions: 22.0x13.0x18.5 (HxWxD) cm

Product weight: 1 kg

F-box dimensions: 22.5x14.0x20.4 (HxWxD) cm

F-box weight: 1 kg

No. of F-boxes in A-box: 6 pcs

A-box dimensions: 24.0x28.8x62.4 (HxWxD) cm

A-box weight: 6.4 kg

Qnt. on Euro pallet: 192 pcs

## Logistic data

CTV code: 884361601000

Country of origin: Germany

## Safety

IEC certified: In line with IEC 60335

## Easy to use

Adjustability: 0-40 degrees (backwards)

On/off switch

