

PHILIPS


HP 4395 salon classic 1600 with diffuser



Power dry




PHILIPS




HP 4395

SALON CLASSIC 1600 WITH DIFFUSER

This semi-professional hair dryer with its unique shape, modern and fresh though referring to classic values of quality, is probably the best offer in terms of drying & styling performance. This 1600W dryer special designed fan gives a very strong airflow resulting in real short drying time without damaging the hair. The product has a temperature limit to ensure your hair is never overheated. Combined with its narrow opening nozzle and its unique volume diffuser this product is also ideal for styling.




Power dry




FEATURES AND BENEFITS

- Low noise : Does not blank out other sounds
- 6 heat/speeds : Covers all drying and styling needs
- Cool shot : For "freezing" the waves or curls
- New volume diffuser : This diffuser which gives a gently even airflow is suitable for both curly and straight hair, it creates a soft natural style and gives the hair more lift near the roots (volume).
- Narrow styling nozzle : For accurate styling
- Non slip pads : To prevent sliding off smooth surfaces
- Hanging loop : Convenient storage
- Detachable inlet filter : Easy cleaning




TECHNICAL SPECIFICATION

- Motor : DC type, long life motor
- Voltage : 220-240; 50-60 HZ and 115 V; 50-60 Hz
- Maximum power consumption : 1600 W
- Materials : Housing: A.B.S., Barrel: Chrome plated metal, Nozzle: P.C., Diffuser: P.C., Outlet grill: P.A., Inlet grill: A.B.S. chrome plated
- Service : Replacement
- EAN code : 87 10103 036487
- CTV code : 8844 395 18000



DIMENSIONS

- Cord length : 2.00 m
- Fancy box : 28.5 x 22.0 x 12.0 cm
- A-box : (4 pcs) 49.0 x 23.5 x 30.0 cm
- Pallet quantity : 240 pcs



Product specification is subject to change without prior notice.