

# Stylers & Colouring

Haircare range 2002



STYLERS									
	HP 4600	HP 4607/PB	HP 4622	HP 4633	HP 4634	HP 4635	HP 4640/01	HP 4644/01	HP 4649/01
<b>Features</b>									
Wattage	200	9,5	300	300	300	300	15	28	330
Settings	1	-	1	1	2	2	-	-	2
Coolshot	-	-	-	-	-	-	-	-	-
Attachments	1 fixed	2 combi	1	2	3	4	1 fixed	1 fixed	2
Straightener	-	-	-	-	-	-	-	●	-
Waterreservoir	-	-	-	-	-	-	●	●	●
Lotion	-	-	-	-	-	-	-	-	●
<b>Logistic data</b>									
Cord length (m)	1,8	1,8	1,8	1,8	1,8	1,8	1,8	1,8	1,8
<i>Dimensions (mm) (LxHxW)</i>									
F-box	310x100x50	98x49x306	110x60x220	170x62x220	170x62x220	230x62x220	320x97x44	318x54x97	285x72x220
A-box	305x215x320	320x210x170	235x235x195	360x205x230	360x205x230	400x250x250	337x210x146	336x232x214	454x306x239
Pieces/A-box	12	6	6	6	6	6	6	8	6
<i>Weight (gr)</i>									
- Product	-	-	-	-	-	-	-	-	-
- F-box	288	290	332	400	444	-	320	450	650
- A-box	-	-	-	-	-	620	2120	3960	5200
Pallet (pcs)	1224/1008	936/1152	960/1200	576/864	576/864	4700	1224/1008	1080	384/288



**PHILIPS**

Let's make things better.



HP 4663



HP 4664



HP 4694



HP 4695



HP 4696



HP 4949

**STYLERS**

	HP 4663	HP 4664	HP 4694	HP 4695	HP 4696	HP 4949
<b>Features</b>						
Wattage	600	600	1000	1000	18	NA
Settings	3	3	3	3	-	NA
Coolshot	-	-	-	-	-	NA
Attachments	3	4	4	5	6	NA
Straightener	-	-	-	-	-	NA
Waterreservoir	-	-	-	-	-	NA
Lotion	-	-	-	-	-	●

**Logistic data**

Cord length (m)	1,8	1,8	1,8	1,8	1,8	NA
Dimensions (mm) (LxHxW)						
F-box	230x62x220	230x62x220	285x70x220	285x70x220	230x60x219	32x68x142
A-box	400x250x250	400x250x250	590x230x230	590x230x230	476x254x238	146x200x155
Pieces/A-box	6	6	6	6	6	12
Weight (gr)						
- Product					-	127
- F-box	620	620	616	616	610	147
- A-box	4700	4700	4720	4720	-	1850
Pallet (pcs)	432/576	432/576	336/384	336/384	448/600	NA



HP 4550



HP 4950

**COLORING**

	HP 4550	HP 4950
<b>Features</b>		
Power	battery	-
Cordless	●	-
Accessories		
Attachment	color diffuser (1 incl.)	diffuser ( 2 per box)