

# PHILIPS

## Curler

32 mm barrel

210°C professional temperature

Ceramic coating

Auto shut-off

HP4684/00



## Perfect bouncy curls and waves

### SalonCurl Pro Curling Iron

Get curling. The SalonCurl Pro is a curling iron with a 38 mm barrel and ceramic tourmaline coating which ensures big bouncy curls and maximum shine

#### Beautifully styled hair

- 38 mm tong for bouncy curls and natural waves
- 210°C professional high heat for perfect salon results

#### Less hair damage


- Ceramic Tourmaline coating for healthy shiny hair
- Digital temperature settings

#### Ease of use

- Ready to use indicator on LCD screen
- Fast heat-up time, ready to use in 60 seconds
- Cool tip for easier and safer use
- Automatic shut-off after 60 min
- Safety stand for easy use
- 1.8 m power cord
- Universal voltage

# Highlights

## 38 mm tong




If you want to create bouncy curls or natural waves, you need curling iron with a wide diameter. 38 mm is the perfect size for creating fashionable wide curls and waves. Truly the professional's choice.

## Ceramic Tourmaline coating



Ceramic Tourmaline coating guarantees perfect heat distribution across the barrel, for shiny results and frizz-free curls.

## 210°C professional temperature



This high temperature enables you change the shape of your hair, and gives you that perfect look, as if you've just come from the salon.

## Digital temperature settings



Digital temperature settings make it easy to quickly choose the function you need or adjust the styling temperature using the digital display. This enables you to select the perfect temperature for your specific needs and type of hair. The result is perfect styling at the touch of a button.

## Instant heat up



The curler has a fast heat up time and is ready to use in 60 seconds.

## Safe usage



Some hair straighteners and curling irons have been equipped with an automatic shut-off feature. This feature has been designed to provide peace of mind. If left on, the appliance will automatically switch off after 60 min.

## Cool tip



The tip of the styler is made from a special heat insulating material to keep it cool; you can safely hold it while you're styling for optimal ease of use.

## 1.8 m cord



1.8 m power cord

## Ready-to-use indicator

Temperature symbol stops blinking when the curler has heated up and ready to use.

## Safety stand

The safety stand enables you to put the curler down safely during use.

## Universal voltage



Worldwide voltage for the perfect travel companion

# Specifications

## Technical specifications

Maximum temperature: 210 °C

Cord length: 1.8 m

Colour/finishing: dark blue and gold

Heater type: PTC ceramic heater

Heating time: 60s

Barrel diameter: 38 mm

Temperature range: digital settings

## Features

Ready for use indicator

Cool tip

Swivel cord

Hanging loop

Ceramic coating

## Hair type

End result: Soft curls and waves

Hair length: Long, Medium

Hair thickness: Thin, Thick, Medium

## Service

2-year worldwide guarantee

