



Philips
Hairdryer

1500W

HP4859

Thermoprotect Super silent 1500

This new Philips beauty hairdryer has been specially designed to meet your personal needs. The Thermoprotect hairdryer features the innovative Thermoflow System that uses more air but less heat.

Beautifully styled hair

- 57C hair protection temperature setting
- 3 flexible speed settings for careful drying
- Narrow nozzle
- Diffuser for volume and bouncy styles

Easy to use

- The most silent hairdryer*
- Hanging loop for easy storage
- Inlet grill; can be opened for easy cleaning
- Foldable handle for easy portability
- Set cool shot; to set your hairstyle in place

PHILIPS
sense and simplicity

Hairdryer
1500W

HP4859/00

Specifications

Technical specifications

- Wattage: 1500 W
- Cord length: 1.8 m
- Color/finishing: golden beige
- Material housing: PC

Serviceability

- Replacement

Features

- Foldable handle
- 2 heat/ speed settings
- Cool shot



Issue date 2011-04-04

Version: 1.0.1

12 NC: 0000 000 00000

© 2011 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips
Electronics N.V. or their respective owners.

www.philips.com