

# PHILIPS

## Hairdryer

1600W

Europe's  
**No.1**  
Hairdryer Brand  
2006-2011\*

\*Based on independent 2011  
cumulated volume sales data for  
17 European countries

HP4961/13



## Quick and easy drying with great results

### SalonDry Compact

#### Beautifully styled hair

- 1600W for gentle drying
- 2 flexible speed settings for careful drying
- Cool Shot sets your style

#### Easy to use

- Compact design for easy handling
- Easy storage hook
- Concentrator focuses the airflow for a polished, shiny look
- 1.8 m cord for maximum flexibility

# Highlights

## 1600W for gentle drying



This 1600W hairdryer creates the optimum level of airflow and gentle drying power, for beautiful results every day.

## 2 flexible speed settings



Careful drying with 2 flexible speed settings

## Cool Shot




A must-have professional function for hair stylers. The Cool Shot button provides an intense burst of cold air. It is used after styling to finish and set the style.

## Compact design



Compact and ergonomic, this hairdryer benefits from a clever modern design. This results in a dryer that is light and easy to handle yet small enough to store virtually anywhere.

## 1.8 m cord



1.8 m cord for maximum flexibility

# Specifications

## Technical specifications

Voltage: 110-127 & 220-240 V

Power: 1600 W

Cord length: 1.8 m

## Features

Cool shot

Hanging loop

## Service

2-year guarantee

