

PHILIPS

Epilator

SatinGirl

Legs & arms

Convenient

Corded



HP6419/05



Great solution to enjoy long-lasting smooth skin
Get hair-free skin for up to 4 weeks.

My SatinGirl epilator is a great way to get rid of unwanted hairs on your legs and arms. It removes hair from the root, leaving your skin smooth for weeks. It's small and easy to take with you when traveling.

Long-lasting smooth skin

- Compact epilator removes body hairs from the root
- Pulls out even the shortest hairs (0.5mm)

Safely removes hair from the root

- The gentle discs work like tweezers, to softly remove hair

Comfortable and convenient hair removal

- Designed for easy holding and comfortable hair removal
- Washable epilation head for extra hygiene and easy cleaning
- Cleaning brush included for quick cleaning
- SatinGirl epilator comes with a 2-year guarantee


Highlights

Compact epilator



SatinGirl epilator has a broad head so that you can quickly remove body hairs. Its small, rounded shape makes it easy to take it along wherever you want.

Efficient root hair removal



Our epilators have uniquely designed precision discs that gently remove hair from the root, catching even the shortest hairs. This means hairs 4x shorter than with wax (0,5 mm), for up to 4 weeks of hair-free skin.

Gentle tweezing discs

The epilator has gentle rotating discs that work like tweezers, softly removing hairs from the root without pulling the skin.

Ergonomic grip

The epilator's rounded shape fits perfectly in your hand for comfortable hair removal.

Washable epilation head



The epilator has a washable head, which can be detached and cleaned under running water.

Cleaning brush

Small cleaning brush to remove loose hairs from the epilator discs.

2-year guarantee



SatinGirl epilator comes with a 2-year guarantee.

Specifications

Features

- Gentle tweezing discs
- 1 speed setting
- Washable epilation head
- Ergonomic grip
- 2 year guarantee

Technical Data (Epilator)

- Number of catching points: 20
- Number of discs: 21
- Pulling actions/sec. speed 1: 600
- Voltage adapter: 13V
- Voltage device: 13 V / 400 mA

Accessories

- Cleaning brush

