

# PHILIPS

## Epilator

### Satinelle

Legs



HP6422/31



## Simply smooth for longer

### Fast and gentle epilator

Enjoy long lasting smoothness with Philips Satinelle epilator. Gently removes hairs, as short as 0.5 mm, from the root. For hair free skin up to four weeks. Includes 2 accessories and a small cleaning brush.

#### Beautiful smooth skin

- Gentle tweezing discs remove hairs without pulling the skin
- Remove hairs as short as 0.5mm

#### Convenient epilation


- Washable epilation head for extra hygiene and easy cleaning
- Two speed settings for gentle epilation and max. performance
- Profiled, ergonomic grip for comfortable handling

#### Accessories

- Opti-start cap with massage element
- Cleaning brush to remove loose hairs from epilator discs
- Convenient pouch for easy storage

# Highlights

## Opti-start with massage cap



For maximum skin contact at all times, whilst relaxing your skin before epilating. This combination of attachment positions the epilator at the optimum angle for a constant and effective hair removal.

## Convenient pouch




Small pouch for easy storage.

## Gentle tweezing discs



This epilator has gentle tweezing discs to remove hairs as short as 0.5mm without pulling the skin.

## Unique epilation discs



Unique epilation discs remove hairs as short as 0.5mm.

## Two speed settings



Extra speed setting for thin hairs and difficult to reach areas

## Washable epilation head



This epilator has a washable epilation head. The head can be detached and cleaned under running water for better hygiene

## Cleaning Brush



Small cleaning brush to remove loose hairs from the epilator discs.

## Ergonomic grip



The rounded shape fits perfectly in your hand for comfortable hair removal

# Specifications

## Features

Gentle tweezing discs  
Unique epilation discs  
2 speed settings  
Washable epilation head  
Ergonomic grip  
2 year guarantee

## Accessories

Opti-start cap: with massage element  
Cleaning brush  
Convenient pouch

## Technical data

Number of catching points: 20  
Number of discs: 21  
Pulling actions/sec. speed 1: 600  
Pulling actions/sec. speed 2: 733  
Voltage adapter: 13V / 400mA  
Voltage device: 13V

