



Body range 2002



HP 6302



HP 6303



HP 6304



HP 6305



HP 6322/00



HP 6324/00



HP 6328/00



HP 6340 PB



HP 6346 PB



HP 6347 PB



HP 6510



HP 5270

LADYSHAVE

DRY/WET & DRY

SOFTSELECT

SKIN COMFORT

WAXING

CLEANSING

	HP 6302	HP 6303	HP 6304	HP 6305	HP 6322/00	HP 6324/00	HP 6328/00	HP 6340 PB	HP 6346 PB	HP 6347 PB
Features										
Moisturising shaving system	-	-	-	-	-	-	-	●	●	●
Gentle shaving system:										
3 zones softselect + 2 trimmers	-	-	-	-	●	●	●	-	-	-
Safe Shaving system	●	●	●	●	-	-	-	-	-	-
Two foils: one for legs and one for underarms/bikini-line	-	-	-	-	●	●	●	●	●	●
Interchangeable softselect foil	-	-	-	-	-	-	-	-	-	-
Exclusive design	●	●	●	●	●	●	●	●	●	●
Rechargeable	-	-	-	●	-	-	-	-	●	●
Mains/battery	-	-	●	-	-	●	-	-	-	-
Mains	-	●	-	-	-	-	-	-	-	-
Battery	●	-	-	-	●	-	-	●	-	-
Wet&Dry usable	●	-	-	●	●	-	●	●	●	●
Removable shaving head for easy cleaning	●	●	●	●	●	●	●	●	●	●
Soft touch for a good grip	●	●	●	●	-	-	-	-	-	-
Accessories										
Protection cap	●	●	●	●	●	●	●	-	-	-
Beauty case	-	-	-	-	-	-	-	-	-	●
Storing cassette	-	-	-	-	-	-	-	●	●	-
Travel Pouch	-	-	-	-	●	●	●	-	-	-
Brush	●	●	●	●	●	●	●	●	●	●
Nivea body shaving lotion sachets	-	-	-	-	-	-	-	●	●	●

Logistic Data

<i>Dimensions (mm) (LxWxH)</i>										
F-box	193x101x69	193x171x65	193x134x69	193x134x69	172x63x192	172x63x192	172x63x192	226x195x81	226x195x81	226x195x81
A-box	310x200x165	397x213x185	410x200x165	410x200x165	400x181x219	400x181x219	400x181x219	365x190x206	365x190x206	400x253x252
Pieces per unit	6	6	6	6	6	6	6	6	6	6
Pallet	390	288	288	210	288	288	288	144	144	144
Weight per product (gr)	102	102	102	130	261	542	402	130	147	147

WAXING	
HP 6510	
Features	
Thermo protect control	●
Pilot light	●
Heat up time (min.)	10
Cordless	●
Stand	●
Accessories	
HP 6901 Wax cartridge	●
Tissue with Almond oil	●
12 paper strips	●

Logistic data	
<i>Dimensions (mm) (LxWxH)</i>	
F-box	68 x 37 x 120
A-box	210 x 205 x 160
Pieces per unit	8 pcs
Pallet	1728
Weight per product (gr)	125 g

CLEANSING	
Bodyvital HP 5270	
Features	
Power source	4x AA batteries (included)
Running time	180 min (alkaline batteries)
Brushes	2
Massage settings	2
Pouch	●
Handstrap	●
Colours	Orchid leaf, lilac

Accessories	
Cleansing brush (HP 5970/00)	●
Exfoliating brush (HP 5971/00)	●

Logistic data	
<i>Dimensions (mm) (LxWxH)</i>	
F-box packaging	165x110x195
A-box packaging	511x236x217
Pieces per A-box	6
Pallet	288
Weight product in packaging	750 gr



PHILIPS

Let's make things better.



HP 2840 PB



HP 2841 PB



HP 6404 PB



HP 6405 PB



HP 6443/00



HP 6444/00



HP 6445/00



HP 6446/00



HP 6433 PB



HP 6434 PB



HP 6435 PB



HP 6437 PB



HP 6438 PB



HP 5215



HP 5233

EPILATORS**BASIC****SATIN ICE****(SUPER) SENSITIVE****CELLESSE**

	HP 2840 PB	HP 2841 PB	HP 6404 PB	HP 6405 PB	HP 6443/00	HP 6444/00	HP 6445/00	HP 6446/00	HP 6433 PB	HP 6434 PB	HP 6435 PB	HP 6437 PB	HP 6438 PB
Features													
Active pain softener, 2 intensities	-	-	-	-	●	●	●	●	-	-	-	-	-
Removable pain softener legs (cleanability)	-	-	-	-	●	●	●	●	-	-	-	-	-
Active pain softener underarms/bikini line	-	-	-	-	-	●	●	●	-	-	-	-	-
Skin cooler	-	-	-	-	-	-	-	-	●	●	●	●	●
Precision cap	-	-	●	-	-	●	-	●	-	●	-	●	●
Exchangeable shaving head	-	-	-	●	-	-	●	-	-	-	●	-	●
Pincette system	●	●	●	●	●	●	●	●	●	●	●	●	●
21 discs	●	●	●	●	●	●	●	●	●	●	●	●	●
2 speeds	-	●	●	●	●	●	●	●	●	●	●	●	●
RPM	2200	I = 1800 II = 2200	I = 1800 II = 2200	I = 1800 II = 2200	I = 1800 II = 2200	I = 1800 II = 2200	I = 1800 II = 2200	I = 1800 II = 2200	I = 1800 II = 2200	I = 1800 II = 2200	I = 1800 II = 2200	I = 1800 II = 2200	I = 1800 II = 2200
Mains	●	●	●	●	●	●	●	●	●	●	●	●	●
Mains & Rechargeable	-	-	-	-	-	-	-	●	-	-	-	-	-
Exclusive design	●	●	●	●	●	●	●	●	●	●	●	●	●
Peeling head	-	-	-	-	-	-	-	-	-	-	-	●	●

Accessories

Protection cap	●	●	●	-	●	●	●	●	●	●	●	●	●
Travel Pouch	●	●	●	-	●	●	●	●	●	●	-	●	-
Luxurious pouch	-	-	-	-	-	-	-	-	-	-	-	-	●
Beauty case	-	-	-	-	-	-	-	-	-	-	-	-	-
Loofah	-	-	-	-	●	●	●	●	-	-	-	-	-
Brush	●	●	●	●	●	●	●	●	●	●	●	●	●
Freezer cassette	-	-	-	-	-	-	-	-	●	●	●	●	●

Logistic Data

<i>Dimensions (mm) (LxWxH)</i>													
F-box	185x60x195	185x60x195	185x60x195	185x60x195	196x68x241	196x68x241	196x68x241	196x68x241	212x224x78	212x224x78	212x224x78	212x224x78	212x224x78
A-box	365x190x206	365x190x206	365x190x206	365x190x206	418x206x265	418x206x265	418x206x265	418x206x265	238x458x245	238x458x245	238x458x245	238x458x245	238x458x245
Pieces per unit	6	6	6	6	6	6	6	6	6	6	6	6	6
Pallet	288	288	288	288	180	180	180	180	168	168	168	168	168
Weight per product (gr)	630	650	653	327	714	717	737	775	863	866	866	876	975

	Cellessé HP 5215	Cellessé Vitesse HP 5233
Features		
Usage time	15 min, 3x per week for 33% reduction	7.5 min, 3x per week for 49% reduction
Wattage	8	8
Vacumotion	●	●
Vacumotion stop	●	●
Personal intensity settings	5	8
Handstrap	●	●
Indicator light	-	●
Pouch	●	●
Colours	blue haze & light lilac	warm white and rosy smoke
Rollers	2 non driven	2 drive, 2 non-driven

Logistic data

<i>Dimensions (mm) (LxWxH)</i>		
F-box packaging	225x157x136	282x176x224
A-box packaging	655x235x160	460x290x190
Pieces per A-box	4	2
Pieces per Pallet	100	50
Weight product in packaging	970 gr	1.67kg