

PHILIPS

Epilator SatinPerfect

Epilate, shape and style

HP6572/00



Smooth in minutes, lasts for weeks

SatinPerfect's extra wide head and textured ceramic discs remove more hair in one stroke, giving you the ultimate epilation experience! Don't you want long-lasting smoothness for up to four weeks? Smooth in minutes, lasts for weeks!

Efficient epilation for long lasting smoothness

- Extra wide head removes more hair in one stroke
- High performance discs gently remove even finest hairs
- Active hairlifter lifts and removes even flat lying hair
- Optimal performance cap pivots for optimal skin contact
- Opti-light reveals even the finest hair

Comfortable epilation


- Vibrating massage bar stimulates and soothes the skin
- Washable epilation head for optimal hygiene

Precious solutions for precious body parts

- Shave, trim and contour for ultra close and smooth results

Highlights

Extra wide head



Extra wide epilation head catches and removes more hair in one stroke for long lasting and super smooth results in minutes

Optimal performance cap



The pivoting movement of the performance cap helps you to keep the epilator at the ideal angle for optimal results

Washable epilation head



This epilator has a washable epilation head. The head can be detached and cleaned under running water for better hygiene

Gentleness system




Gently vibrating massage bar stimulates and soothes the skin for a pleasant epilation process

Shave, trim and style




Shave, trim and contour for ultra close and smooth results

High performance discs




Textured high performance ceramic discs prevent even the finest hair slipping through

Opti-light



Built-in Opti-light reveals tiny, fine hairs clearly

Unique hairlift&vibrate system



Unique hairlift&vibrate system uses subtle vibrations to lift fine hairs, making it easy to remove them

Specifications

Fast, long lasting epilation

Extra wide head
Textured ceramic tweezers
Active hair lifter
Opti-light
Optimal performance cap
Hair primer
Body contouring head
Pressure control

Comfortable epilation

Gentleness system
Two speed settings

Convenience and hygiene

Washable epilation head
Luxury pouch
Cleaning brush

Precious and luxury solutions

Shave, trim and contour

Technical details

Colour: Cerise
Number of tweezers: 32
Rotations per minute: 2550
Catching actions per minute: 81,600
Mains epilator
Voltage: 100–240 V
Wattage: 16
Frequency: 50–60 Hz

