

PHILIPS

Epilator

SatinPerfect

Total body

Cordless



HP6572/50



Smooth in minutes, lasts for weeks

Fast and efficient epilator

SatinPerfect's extra wide head and textured ceramic tweezers remove more hair in one stroke, giving you the ultimate epilation experience! Don't you want long lasting smoothness for up to four weeks? Smooth in minutes, lasts for weeks!

Comfortable epilation

- Up to 40 minutes wirefree epilation, quick 1-hour recharge
- Fully washable epilation head for optimal hygiene

Efficient epilation for long lasting smoothness

- Built-in opti-light reveals tiny, fine hairs
- Extra speed setting: gentle epilation or faster performance
- Speed control technique maintains the ideal epilation speed
- Hypo allergenic textured ceramic discs gently remove hairs


Highlights

Cordless




Epilate anywhere with this cordless epilator. Up to 40 minutes wirefree wplation, quick 1-hour recharge.

High performance discs




Hypo allergenic textured High performance ceramic discs prevent even finest hairs from slipping through. You will not miss any hairs!

Opti-light



Opti-light helps to indicate and light up even the finest hair for smooth and hair free skin

Speed control technique



Speed control technique maintains the ideal epilation speed as a pressure control to protect your skin

Two Speed Settings



Speed 1 for extra gentle epilation and speed 2 for faster performance

Washable epilation head



The head can be detached and cleaned under running water for better hygiene

Specifications

Comfortable epilation

Cordless
Two speed settings

Convenience and hygiene

Cleaning brush
Luxury pouch
Washable epilation head

Fast epilation, long lasting

Extra wide head
Opti-light
Ergonomically shaped head
Speed control

Technical facts

Catching actions per minute: 81.600
Charge time: 1 hour(s)
Colour: Purple
Cordless/recharge -epilator
Frequency: 50-60 Hz
Mains -epilator
Number of catching points: 32
Rotations per minute: 2550
Runtime main epilator: 40 min
Voltage: 100-240 V
Wattage: 16

