

PHILIPS

Epilator

SatinPerfect

Total body

Cordless



HP6574/50



Smooth in minutes, lasts for weeks

Fast and gentle epilator

SatinPerfect epilator's extra wide head and textured ceramic tweezers remove more hair in one stroke, giving you the ultimate epilation experience! Don't you want long lasting smoothness for up to four weeks? Smooth in minutes, lasts for weeks!

Active vibrating hairlift system primes hairs

- Active hairlifter vibrates and removes even flat-lying hairs

Comfortable epilation

- Up to 40 minutes wirefree epilation, quick 1-hour recharge
- Washable epilation head for optimal hygiene
- Active massaging system stimulates and soothes the skin

Efficient epilation for long lasting smoothness

- Opti-light reveals even the finest hair
- Curved head follows every contour of your body
- Hypo allergenic textured ceramic discs gently remove hairs
- Pressure control gives you always the ideal epilation speed

Highlights

Cordless



Epilate anywhere with this cordless epilator. Up to 40 minutes wirefree epilation, quick 1-hour recharge.

Opti-light

Built in Opti-light reveals tiny, fine hairs clearly

Washable epilation head



This epilator has a washable epilation head. The head can be detached and cleaned under running water for better hygiene

Active hairlift&vibrate system




Active hairlifter vibrates and removes even flat-lying hairs

Active massaging system




Active massaging system stimulates and soothes the skin

Body contouring head




Curved head follows every contour of your body

Hypo-allergenic ceramic discs



Gently grip and remove finest hairs

Pressure control



Pressure control gives you always the ideal epilation speed

Specifications

Accessories

Luxury pouch
Opti-light

Comfortable epilation

Cordless
Two speed settings

Design

Color: White & pink

Fast epilation, long lasting

Active hair lifter

Technical facts

Frequency: 50-60 Hz
Mains -epilator
Number of catching points: 32
Rotations per minute: 2550
Runtime main epilator: 40 min
Voltage: 100-240 V
Wattage: 16

