

# PHILIPS

## Epilator

### SatinPerfect

Luxury depilation set

Cordless

HP6578/00



## Smooth in minutes, lasts for weeks

SatinPerfect's extra wide head and textured ceramic discs remove more hair in one stroke, giving you the ultimate epilation experience! Don't you want long lasting smoothness for up to four weeks? Smooth in minutes, lasts for weeks!

### Efficient epilation for long lasting smoothness

- Extra wide head removes more hair in one stroke
- High performance discs gently remove even finest hairs
- Active hairlifter lifts and removes even flat lying hair
- Optimal performance cap pivots for optimal skin contact
- Opti-light reveals even the finest hair

### Comfortable epilation

- Vibrating massage bar stimulates and soothes the skin
- Washable epilation head for optimal hygiene
- Up to 40 minutes wirefree epilation, quick 1-hour recharge

### Precious solutions for precious body parts

- Shave, trim and contour for ultra close and smooth results
- Cordless mini epilator for precise details
- Luxury additional portable tweezers with light and mirror

# Highlights

## Cordless



Epilate anywhere with this cordless epilator. Up to 40 minutes wirefree epilation, quick 1-hour recharge.

## Optimal performance cap




The pivoting movement of the performance cap helps you to keep the epilator in the ideal angle for optimal results

## Unique hairlift&vibrate system



Unique hairlift&vibrate system uses subtle vibrations to lift fine hairs, making it easy to remove them

## Extra wide head



Extra wide epilation head encounters and removes more hair in one stroke for long lasting and super smooth results in minutes

## Cordless precision epilator



A precious solution for precious body parts. Slender, gentle precision epilator ideal for sensitive area's and travelling.

## Washable epilation head



This epilator has a washable epilation head. The head can be detached and cleaned under running water for better hygiene

## Gentleness system




Gently vibrating massage bar stimulates and soothes the skin for a pleasant epilation process

## Shave, trim and style




Shave, trim and contour for ultra close and smooth results

## High performance discs



Textured high performance ceramic discs avoid even finest hair slipping through

## Opti-light



Built in Opti-light reveals tiny, fine hairs clearly

## Smart tweezers



Tweezers in an elegant case, with integrated light and mirror, ideal for eyebrows

# Specifications

## Fast epilation, long lasting

Extra wide head  
Ceramic textured discs  
Active hair lifter  
Opti-light  
Optimal performance cap  
Hair primer  
Body contouring head  
Pressure control

## Comfortable epilation

Cordless  
Gentleness system  
Two speed settings

## Convenience and hygiene

Washable epilation head  
Luxury pouch  
Cleaning brush

## Precious and luxury solutions

Shave, trim and contour  
Cordless precision epilator  
Luxury tweezer set

## Technical facts

Colour: Purple metallic  
Number of catching points: 32  
Rotations per minute: 2550  
Catching actions per minute: 81.600

## Mains -epilator

Cordless/recharge -epilator  
Charge time: 1 hour(s)  
Runtime main epilator: 40 min  
Cordless precision epilator  
Precision epilator batteries: 2x AA  
Runtime precision epilator: 60 min  
Voltage: 100-240 V  
Frequency: 50-60 Hz

