

PHILIPS

Hairdryer

1000W

HP8100/00



Easy care for your hair

Salon Compact Hair dryer

Beautifully styled hair

- 1000W for beautiful results
- 2 flexible speed settings for careful drying
- Narrow concentrator for focused airflow

Easy to use

- Compact design for easy handling
- Easy storage hook for convenient storage
- 1.5 m power cord

Highlights

Specifications

1000W



This 1000W hairdryer creates the optimum level of airflow and gentle drying power, for beautiful results every day.

Compact design




Compact and ergonomic, this hairdryer benefits from a clever modern design. This results in a dryer that is light and easy to handle yet small enough to store virtually anywhere.

2 flexible speed settings



Careful drying with 2 flexible speed settings

Narrow concentrator



The concentrator works by focusing the flow of air through the opening onto specific areas. This results in precise styling and is great for touch ups or to finish a style.

Easy storage hook



The rubberised hook is located at the base of the handle and provides another storage option, particularly convenient for use in the home or when staying at a hotel.

Technical specifications

Wattage: 1000 W
Cord length: 1.5 m

Features

Hanging loop

Service

2-year guarantee

