

PHILIPS

Hairdryer

1000W



HP8100/46



Extra gentle drying for your hair

Cleverly designed, this compact hair dryer is easy to handle and lightweight. The ThermoProtect temperature setting provides the optimal hair drying rate while protecting your hair from overheating.

Beautifully styled hair

- 1000W for beautiful results
- 2 flexible heat settings for careful drying
- Narrow concentrator for focused airflow

Easy to use

- ThermoProtect temperature setting
- Compact design for easy handling
- Easy storage hook for convenient storage
- 2 years of worldwide guarantee


Highlights

1000W



This 1000W hairdryer creates the optimum level of airflow and gentle drying power, for beautiful results every day.

2 flexible heat settings



Careful drying with 2 flexible heat settings.

ThermoProtect temperature



The ThermoProtect temperature provides the optimal drying temperature and gives additional protection from overheating the hair. With the same powerful airflow, you will get the best results in a caring way.

Compact design




Compact and ergonomic, this hairdryer benefits from a clever modern design. This results in a dryer that is light and easy to handle yet small enough to store virtually anywhere.

Easy storage hook



The rubberised hook is located at the base of the handle and provides another storage option, particularly convenient for use in the home or when staying at a hotel.

Narrow concentrator



The concentrator works by focusing the flow of air through the opening onto specific areas. This results in precise styling and is great for touch ups or to finish a style.

2 years guarantee



2 years of worldwide guarantee.

Specifications

Technical specifications

Wattage: 1000 W

Cord length: 1.5 m

ThermoProtect setting

Features

Hanging loop

Narrow Concentrator

Service

2-year guarantee

