

Hairdryer

KeraShine

IonBoost

HP8119/00



Shine therapy for silky smooth hair

This 1200W hair dryer comes with a ThermoProtect setting and Keratin coating to ensure maximum care during your drying experience. The ionic technology ensures you will minimize frizz and achieve the beautiful shiny results you desire.

Beautifully styled hair

- 1200W gentle drying for beautiful results
- Three flexible settings for more control

Less Hair Damage

- ThermoProtect
- Cool air setting for gentle drying
- Care for your hair with the keratin-infused ceramic coating
- Ionic conditioning for shiny, frizz-free hair


Easy to use

- Foldable handle for easy portability
- Integrated nozzle for more efficient drying
- Easy storage hook for convenient storage

Highlights

1200W

This 1200W hairdryer creates the optimum level of airflow and gentle drying power for beautiful results every day.

Ionic conditioning

Give your hair instant care with ionic conditioning. Charged negative ions eliminate static, condition your hair, and smooth the hair cuticles to intensify hair's shine and glossiness. The result is smooth and frizz-free hair with beautiful shine.

ThermoProtect

As built-in protection for your hair, ThermoProtect retains a constant caring temperature. This allows you to quickly dry your hair without over-drying, maintaining your hair's natural moisture level for shiny, healthy looking hair.

Ceramic Keratin Coating

The keratin-infused ceramic nozzle provides an extra layer of care. Keratin helps your hair retain its natural strength and shine.

Three flexible settings

The speed and heat required can be easily adjusted to create the perfect end result. Three flexible settings ensure precise and tailored styling.

Cool air setting

A cold air setting is a low heat setting that gently dries the hair to minimize damage. This function is suitable for all hair types, but especially for fine, dry or damaged hair. It's a perfect setting for the hot summer season!

Easy storage hook

The rubberised hook is located at the base of the handle and provides another storage option, particularly convenient for use in the home or when staying at a hotel.

Foldable handle

This hairdryer benefits from a foldable handle. The result is a small, compact hair dryer that will easily pack into the smallest spaces and you can take virtually anywhere.

Efficient integrated nozzle

A unique dryer where the nozzle is integrated into the streamlined design - for maximum drying efficiency.

Specifications

Technical specifications

Wattage: 1200 W
Cord length: 1.5 m
ThermoProtect setting

Features

Foldable handle
Cool shot
Settings: 3 heat/speed settings
Hanging loop
Ionic conditioning

Service

2-year guarantee

