

# PHILIPS

## Hairdryer

### SalonShine Care



HP8203/00



## Ion conditioning for frizz-free hair SalonShine Care ION

Get the style you want whilst looking after your hair. The SalonDry Pro offers 1600W of professional drying power.

### Beautifully styled hair

- Specially designed for Asians
- 1600W for gentle drying
- Six flexible speed and temperature settings for full control
- 100% more Ions for ultimate shine
- Coolshot for seal in shine and fix your style
- Narrow concentrator for focused airflow
- Volume diffuser enhances volume, for curls and bouncy styles

### Less Hair Damage

- EHD+ technology for more protection and shinier results
- Best drying temperature with ThermoProtect temperature

### Easy to use

- Foldable handle for easy portability
- Compact design for easy handling
- 1.5 m power cord

# Highlights

## Specially designed for Asians




Specially designed for Asians

## 1600W for gentle drying



This 1600W hairdryer creates the optimum level of airflow and gentle drying power, for beautiful results every day.

## EHD+ technology



Advanced Philips EHD+ technology means that your dryer will always distribute the heat very evenly - even at high temperatures, and prevents damaging hot spots. This gives added protection and thus helps to keep your hair healthy and shiny.

## Six flexible speed and temperature settings



The speed and heat required can be easily adjusted to create the perfect style. Six different settings ensure full control for precise and tailored styling.

## 100% more Ions

100% more Ions for ultimate shine

## Coolshot



Coolshot for seal in shine and fix your style

## Easy storage hook




The rubberised hook is located at the base of the handle and provides another storage option, particularly convenient for use in the home or when staying at a hotel.

## 1.5 m power cord

1.5 m power cord

## Narrow concentrator



The concentrator of the hair dryer works by focusing the flow of air through the opening onto specific areas. This results in precise styling and is great for touch ups or to finish a hair style.

## Volume diffuser



The volume diffuser dries hair healthily, reduces frizz and increases volume by spreading the airflow across the hair. It adds lift and maximises volume, especially when used on the crown and root area, making it perfect for creating curls and bouncy styles

## Foldable handle



This hairdryer benefits from a foldable handle. The result is a small, compact hair dryer that will easily pack into the smallest spaces and you can take virtually anywhere.



# Specifications

## Technical specifications

Wattage: 1600 W

## Features

Cool shot  
Foldable handle  
Hanging loop

## Service

2-year guarantee

