

PHILIPS

Hairdryer

Shine & Protect

Titanium Collection
with Volume Diffuser



HP8219/03



Titanium Collection : Extra Shine,Ultimate Protect

The exclusive Titanium Shine & Protect collection brings you fast drying results whilst protecting your hair from overheating with the advanced Titanium Ionic Care, ThermoProtect and EHD™ Technology.

Beautifully styled hair

- Volume diffuser enhances volume, for curls and bouncy styles
- 1600W for gentle drying
- Titanium Ionic Care Design

Less Hair Damage

- Less overheating with Even Heat Distribution technology
- ThermoProtect

Easy to use

- Six flexible speed and temperature settings for full control


Highlights

Titanium Ionic Care Design



The new Titanium Ionic Care Design instantly releases 2X ions for an effective anti-static effect. The results is : shiny, smooth & frizz-free hair. The unique Titanium coating of the ion generator ensure a better corrosion resistance for great results. Love your hair, let it shine!

Advanced EHD technology



Advanced Philips EHD technology means that your dryer uses an uniquely designed air outlet to ensure heat is always distributed very evenly - even at high temperatures - and prevents damaging hot spots. This gives ultimate protection to the hair from overheating and thus helps to keep your hair healthy and shiny.

ThermoProtect



As built-in protection for your hair, ThermoProtect retains a constant caring temperature. This allows you to quickly dry

your hair without over-drying, maintaining your hair's natural moisture level for shiny, healthy looking hair.

1600W for gentle drying



This 1600W hairdryer creates the optimum level of airflow and gentle drying power, for beautiful results every day.

Six flexible speed and temperature settings



The speed and heat required can be easily adjusted to create the perfect style. Six different settings ensure full control for precise and tailored styling.

Volume diffuser



The volume diffuser dries hair healthily, reduces frizz and increases volume by spreading the airflow across the hair. It adds lift and maximises volume, especially when used on the crown and root area, making it perfect for creating curls and bouncy styles

Specifications

Technical specifications

Wattage: 1600 W

Cord length: 1.6 m

Voltage: 220 V

Features

Settings: 6 heat/speed settings

Hanging loop

Service

2-year guarantee

Accessories

Attachments: Nozzle, Volume diffuser

Design

Color: Premium champagne gold

