

PHILIPS

Hairdryer

DryCare Advanced

ThermoProtect

2100 W

6 heat and speed settings

Cool shot



HP8230/00



Fast dry at a lower temperature with ThermoProtect with 14 mm styling nozzle.

Protect your hair while still enjoying fast drying results. Choose from multiple speed and temperature settings to get the blow dry you want or select ThermoProtect for fast drying at a constant caring temperature.

Beautifully styled hair

- Professional 2100 W for perfect salon results
- Six flexible speed and temperature settings for full control
- Perfect styling results with a slim styling nozzle
- Cool Shot sets your style

Less Hair Damage

- ThermoProtect temperature setting

Easy to use

- 1.8 m power cord
- Easy storage hook for convenient storage
- Removable air flow filter makes cleaning quick and easy



asimpleswitch.com

Highlights

ThermoProtect temperature



The ThermoProtect temperature provides the optimal drying temperature and gives additional protection from overheating the hair. With the same powerful airflow, you will get the best results, whilst being kind to your hair.

Professional 2100 W



This 2100 W professional hairdryer creates a powerful airflow. The resulting combination of power and speed makes drying and styling your hair quicker and easier.

Speed and temperature settings



The speed and heat required can be easily adjusted to create the perfect style. Six different settings ensure full control for precise and tailored styling.

Cool Shot



A must-have professional function for hair stylers. The Cool Shot button provides an intense burst of cold air. It is used after styling to finish and set the style.

Slim styling nozzle



Perfect styling results and a shiny, polished look with a slim styling nozzle for precise styling.

1.8 m cord



Convenient to use thanks to the 1.8-m power cord length.

Easy storage hook



The rubberised hook is located at the base of the handle and provides another storage option, particularly convenient for use in the home or when staying at a hotel.

Removable air inlet filter

The removable air flow filter of your hairdryer is easy to maintain. Simply click off to clean. Doing this regularly will prevent build-up of dust and hair that can affect drying performance.



[asimpleswitch.com](https://www.asimpleswitch.com)

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas — Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Technical specifications

Voltage: 220-240 V

Frequency: 50-60 Hz

Wattage: 2100 W

Power: 2100 W

Colour/finishing: High Gloss and Matt Black

Housing material: ABS

Motor: DC Motor

Cord length: 1.8 m

Features

Foldable handle: No

Cool shot

Dual voltage: No

Travel pouch: No

Ceramic coating: No

Ion conditioning: No

Hanging loop

Diffuser: No

Nozzle / Concentrator: Slim 14-mm styling nozzle

Number of attachments: 1

Service

2 year guarantee

Weight and dimensions

A-Box Dimensions: Height = 25 cm, Length = 63cm, Width = 35cm

A-Box Weight: 5.7 kg

F-Box Dimensions: Depth = 11cm, Height = 23cm, Width = 31cm

F-Box weight: 0.8 kg

Product size: Height = 31 cm, Length = 10 cm, Width = 22cm

Product weight (excl. pack): 0.6 kg

