

PHILIPS

Hairdryer

DryCare Advanced

1500W



HP8243/01



Fast dry at a lower temperature with ThermoProtect with volume diffuser & 11mm styling nozzle.

Protect your hair while enjoying fast drying results. This hair dryer has multiple speed and temperature settings. Features include ThermoProtect for fast drying at a constant caring temperature, Ionic Care & TurboBoost.

Beautifully styled hair

- Professional 1500W
- Ultra slim styling nozzle of 11mm for precision styling
- Turbo boost for extra fast drying
- Adds volume, maximising thickness, curls and bouncy styles
- Six flexible speed and temperature settings for full control
- Cool Shot sets your style

Less Hair Damage

- ThermoProtect temperature setting
- Ionic conditioning for shiny, frizz-free hair

Easy to use

- Elegant, feminine design emphasising performance and quality
- 1.8 m power cord
- Easy storage hook for convenient storage

Highlights

1500W



This 1500W professional hairdryer creates a powerful airflow. The resulting combination of power and speed makes drying and styling your hair quicker and easier.

Premium Design



This hairdryer embodies a modern, sophisticated approach to design. Soft, fluid contours and elongated proportions subtly communicate femininity while precision detailing and high quality materials and finishes are evidence of the product's superior performance.

ThermoProtect temperature



The ThermoProtect temperature provides the optimal drying temperature and gives additional protection from overheating the hair. With the same powerful airflow, you will get the best results in a caring way.

Ionic conditioning



Give your hair instant care with ionic conditioning. Charged negative ions eliminate static, condition your hair, and smooth the hair cuticles to intensify hair's shine and glossiness. The result is smooth and frizz-free hair with beautiful shine.

Speed and temperature settings



The speed and heat required can be easily adjusted to create the perfect style. Six different settings ensure full control for precise and tailored styling.

Ultra slim styling 11mm nozzle



The ultra thin styling nozzle concentrates the flow of hair through the 11mm nozzle for precision styling on specific areas. Great for touch ups or to set your style.

Turbo boost



The turbo boost button increases the airflow, to dry your hair even quicker.

Asymmetric volume diffuser



The volume diffuser has a unique asymmetric design that is contoured to the head, making it easier and more intuitive to use. The diffuser also spreads the flow of air across the hair, drying hair more healthy, boosting volume and reducing frizz. For best results, hold close to the crown and root area and let the diffuser's fine textured pins encourage volume, add bounce and shape curls.

Cool Shot



A must-have professional function for hair stylists. The Cool Shot button provides an intense burst of cold air. It is used after styling to finish and set the style.

Specifications

Technical specifications

Voltage: 110 V

Frequency: 50-60 Hz

Wattage: 1500 W

Power: 1500 W

Color/finishing: Glossy Black & Gold

Housing material: PC

Motor: DC Motor

Cord length: 1.8 m

Features

Cool shot

Ion conditioning

Hanging loop

Diffuser: Massaging volume diffuser

Nozzle / Concentrator: Ultra slim styling 11mm nozzle

Number of attachments: 2

Service

2-year guarantee

Weight & dimensions

Product size: Width = 22cm, Height = 31cm, Length = 10cm

Product weight (excl. pack): 0.6kg

